



Photo Not Available



BURNDY Catalog Number	YSL29
UPC Number	7818104188022
Description	CANADA YSL SPLCE 250KCML
Status	Active

Web Use
BURNDY Product Line

Strip Length
Length (in)
Barrell Style
Barrel Type

Dimensional

1-1/8
2.46
Chamfered
Standard

Product Description

General

Copper Compression Splice, 250
kcmil, 2.46" Splice Length, Short
Barrel, Tin Plated

Type of Plating
Plated (Yes or No)
Index Number
Product Material

Physical

Tin - Electro Plated
Y
16
Copper

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Documentation

Approvals / Certifications

Y
Y
Compliant
N
N

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175