

# CADDY PYRAMID

## Rooftop Support System



- Protects roof membranes
- Superior load distribution
- Broad range of applications
- Fast and easy to install



## CADDY SPEED LINK



CADDY SPEED LINK

# CADDY SPEED LINK

## CADDY SPEED LINK Y-Hook with Eyelet Extension

- Double hook offers easy attachment to basket tray, cable tray or lighting
- Convenient design allows one hook to be temporarily detached for maintenance or to add cables to the tray
- Y-design provides improved stability
- Spring latch helps provide secure connection



Material: Steel

Finish: Electrogalvanized

Static Load Safety Factor: 5:1



Part Number	Description	F ↓
Wire Rope Diameter: 2 mm		
SLD2YH500	2 mm Wire, 19.6" Y-Length	100 lb
SLD2YH800	2 mm Wire, 31.4" Y-Length	100 lb
Wire Rope Diameter: 3 mm		
SLD3YH500	3 mm Wire, 19.6" Y-Length	200 lb
SLD3YH800	3 mm Wire, 31.4" Y-Length	200 lb

CADDY SPEED LINK locking device not included.

## CADDY SPEED LINK Y-Toggle with Eyelet Extension

- Attaches to clearance holes in a variety of structures or hanging devices
- Ideal for supporting lighting fixtures
- Y-design provides improved stability



Material: Steel

Finish: Electrogalvanized

Static Load Safety Factor: 5:1



Part Number	Description	F ↓		Certifications
Wire Rope Diameter: 1.5 mm				
SLD15Y200	1.5 mm Wire, 7.8" Y-Length	44 lb	20 pc	cULus
SLD15Y300	1.5 mm Wire, 11.8" Y-Length	44 lb	20 pc	cULus
SLD15Y500	1.5 mm Wire, 19.6" Y-Length	44 lb	20 pc	cULus
SLD15Y500R2	1.5 mm Wire, 19.6" Y-Length	44 lb	10 x 2 pc	-
SLD15Y800	1.5 mm Wire, 31.4" Y-Length	44 lb	20 pc	cULus
SLD15Y800R2	1.5 mm Wire, 31.4" Y-Length	44 lb	10 x 2 pc	-
Wire Rope Diameter: 2.0 mm				
SLD2Y300	2 mm Wire, 11.8" Y-Length	100 lb	20 pc	cULus
SLD2Y500	2 mm Wire, 19.6" Y-Length	100 lb	20 pc	cULus

CADDY SPEED LINK locking device not included.