
WALL PLATES & SPECIALTIES



SWP26LA

Screwless Polycarbonate Wall Plates

- A. Molded of rugged .065" thick polycarbonate.
- B. Seamless, sleek, super smooth construction provides no dirt-catching channel around plate's perimeter.
- C. Two-piece plastic subplate bridges recessed boxes and uneven sheet rock. Fixes floating installations.
- D. Automatic alignment pins ensure that devices are properly positioned so that wall plates fit perfectly.
- E. Oversized opening to accommodate all NEMA 26 decorator-style openings.
- F. An extra 1/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.



Specifications















Thermoset SP Series

Nylon TP Series

Screwless Polycarbonate SWP Series

302/304 Stainless Steel

Polished Brass

ed

Brushed Brass

Aluminum

Application

Legrand's broad line of Pass & Seymour® Standard Size Plastic and Metal Wall Plates features the most complete range of types, sizes, colors, and finishes available. Choose from more than 1,900 standard plates in non-combustible thermoset plastic material, self-extinguishing nylon material, screwless polycarbonate material, or attractively finished metal, for residential, commercial, institutional, and industrial applications. All plastic wall plates color match to Pass & Seymour devices.

Thermoset Plastic Wall Plates

- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent and moisture.
- Nominal thickness, .070"

TradeMaster® Thermoplastic Wall Plates

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only)
- Available in "TP" series, extra 3/16" width and height than Standard size plates; and "TPJ" series, extra 3/16" width and height than Junior-Jumbo size plates
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070"

Screwless Polycarbonate Wall Plates

- Molded of .065" thick polycarbonate, matte finish.
- 2-piece plastic subplate made of polycarbonate.
- Extra 1/8" width and height than Standard size plates.
- Available in Ivory, White, Brown, Gray, Black, and Light Almond; and three metallic finishes.


Metal Wall Plates

- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze or galvanized steel.
- Standard, Jumbo, and Tandem size plates available, as well as special Panel size plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes. Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Materials

- Type 302/304 Stainless Steel, non-magnetic, .032" nominal thickness, brushed finish. This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Type 430 Stainless Steel, magnetic, .032" nominal thickness, brushed finish. Less corrosion-resistant than Type 302/304, but ideal for general service in high abuse applications in industrial plants, commercial, and institutional buildings.
- Chrome, Brushed and Polished Brass, .040" thick. 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications. Lacquered to prevent corrosion.
- Aluminum, .040" thick. Lustrous satin finish. Lacquered to prevent corrosion.
- Galvanized Steel. Used only for Handy Box Plates.
- Brushed Bronze, .040" thick. 90% copper, 10% zinc. Lacquered to prevent corrosion.

Dimensions



Standard Size Wall Plates

- Standard size wall plates for all applications.
- Best fit for surface mount boxes.
- · Available in plastic and metal only.

Dimensions

1 gang 2.75" x 4.5" 2 gang 4.56" x 4.5" 3 gang 6.375" x 4.5" 4 gang 8.125" x 4.5" 5 gang 10" x 4.5" 6 gang 11.812" x 4.5" 13.62" x 4.5" 7 gang 15.44" x 4.5" 8 gang

TradeMaster® Wall Plates

- Extra 3/16" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle and decorator single gang plates.

Dimensions

1 gang 2.9375" x 4.6875"
2 gang 4.75" x 4.6875"
3 gang 6.563" x 4.6875"
4 gang 8.375" x 4.6875"
5 gang 10.188" x 4.6875"
6 gang 12" x 4.6875"

Screwless Polycarbonate Wall Plates

- Available in decorator openings.
- Extra 1/8" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Molded of .065" thick polycarbonate.
- 2-piece plastic subplate made of polycarbonate.
- Available in 3 metallic finishes and 6 standard colors.

Wall Plate Dimensions

1 gang 3.10" x 4.87" 2 gang 4.912" x 4.87" 3 gang 6.724" x 4.87" 4 gang 8.536" x 4.87"

Subplate Dimensions

1 gang 2.85" x 4.62" 2 gang 4.662" x 4.62" 3 gang 6.474" x 4.62" 4 gang 8.286" x 4.62"

Junior-Jumbo Wall Plates

- Extra 3/8" width and height than Standard size wall plates.
- Additional coverage for sheet rock gaps.
- Available in plastic and metal only.

Dimensions

1 gang 3.125" x 4.87" 2 gang 4.93" x 4.87" 3 gang 6.75" x 4.87" 4 gang 8.56" x 4.87"

TradeMaster® Jumbo Wall Plates

- Extra 3/16" width and height than Junior-Jumbo size wall plates.
- Provide additional coverage for sheet rock gaps, matching the appearance of the TradeMaster Plates.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle, and decorator single gang plates.

Dimensions

1 gang 3.3125" x 5.0625" 2 gang 5.125" x 5.0625" 3 gang 6.9375" x 5.0625" 4 gang 8.75" x 5.0625"

Jumbo Wall Plates


- Extra 3/4" width and height than Standard size wall plates.
- Largest size wall plates to cover larger wall damage.
- Available in plastic and metal only.

Dimensions

1 gang 3.5" x 5.25" 2 gang 5.31" x 5.25" 3 gang 7.12" x 5.25" 4 gang 8.93" x 5.25"



Dimensions




Sectional Wall Plates

End and center panels with each of five most-used configurations make it possible to improvise custom wall plates on the job. Panels lock securely together on installation. Blank sections furnished with mounting strap.


Wall Plate Mountings

Illustrated are the five standard methods of plate mounting. There are many other non-standard methods which depend upon the special device used. Exact mounting hole specifications for every device appear in the Selector Guide.





Wall Plate Sizes

Standard Size




TradeMaster® Size Available in nylon only







TradeMaster Jumbo Available in nylon only



Jumbo




Tandem Wall Plates



Metal only. Plate mounting dimensions are non-standard. Refer to Page P-26 for details and devices that can be used.

Screwless Wall Plate Plastic Subplate



For Screwless (SWP) Wall Plate dimensions refer to Page P-4.

WALL PLATES


Decorator Openings Standard Size Plastic & Metal


		NYLON	THERMOSET	METAL	
DESCRIPTION	COLOR	TRADEMASTER® PLATES	SM00TH	MATERIAL	SMOOTH
DECORATOR OPENINGS					
Two Gang	Ivory White Brown	TP262I TP262W TP262	SP262I SP262W SP262	Aluminum Brass	SA262 SB262
••	Gray Black Red Light Almond	TP262GRY TP262BK TP262RED TP262LA	SP262GRY SP262BK SP262LA	Polished Brass 430S/S 302/304 S/S	SB262PB SL262 SS262
Three Gang	Blue Orange Ivory	TP262BL TP2620R TP2631	SP263I		
	White Brown Gray	TP263W TP263 TP263GRY	SP263W SP263GRY	Brass Polished Brass	SB263 SB263PB
	Black Red Light Almond Ivory	TP263BK TP263RED TP263LA TP264I	SP263LA SP264I	302/304 S/S	SS263
Four Gang	White Brown Gray	TP264W TP264 TP264GRY	SP264W SP264 SP264GRY	Brass Polished Brass	SB264 SB264PB
	Black Red Light Almond	TP264BK TP264RED TP264LA	SP264BK SP264LA	302/304 S/S	SS264
Five Gang	lvory White Brown Gray Black Red Light Almond	TP265I TP265W TP265 TP265GRY TP265BK	SP265I SP265W SP265GRY SP265BK SP265RED SP265LA	302/304 S/S	SS265
Six Gang	lvory White Brown Gray	TP266I TP266W TP266 TP266GRY	SP266I SP266W SP266 SP266GRY	302/304 S/S	SS266
Seven Gang	Black Light Almond	TP266BK TP266LA	SP266BK SP266LA	302/304 S/S	SS267
				302/304 S/S Painted Ivory 302/304 S/S Painted White	SS267I SS267W
Eight Gang				302/304 S/S 302/304 S/S Painted Ivory 302/304 S/S Painted White	SS268 SS268I SS268W


Custom Metal Wall Plates Special Configurations

Chart B: Paint Finish Selection

These charts are for Custom Metal Wall Plates ONLY. For Devices & Wall Plates Color Selection Charts, see Pages A-29, B-87 and P-58.







Only available on Stainless Steel and Aluminum Plate Material. Colors may vary slightly. All Paint Finishes are gloss, except primer and flat black.

Chart C: Metal Finish Selection



Bright Chromium US #26 СН



Brushed Copper ВС



Brushed Bronze US #10 ΒZ



Brushed Brass Standard Finish ВВ

For additional colors consult factory.

FINISH SUFFIX PB*

^{*}Order with Brass Plate Material Prefix Only.