

# Tapping Tools and Awls

## Cushion-Grip Triple Taps and Six-in-One Tap Tool

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.

| Cat. No. | Tap Sizes  | Overall Length | Weight (lbs.) |
|----------|--|----------------|---------------|
| 623-20   | Triple Tap 10-24, 12-24, 1/4-20                    | 7-3/4"         | .25           |
| 623-24   | Triple Tap 6-32, 8-32, 10-24                       | 7-3/4"         | .25           |
| 623-32   | Triple Tap 6-32, 8-32, 10-32                       | 7-3/4"         | .25           |
| 626      | 6-in-1 Tap 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20 | 7-3/4"         | .25           |



626

### Replacement Taps

|        |                      |                             |
|--------|----------------------|-----------------------------|
| 628-20 | 10-24, 12-24, 1/4-20 | replacement for 623-20, 626 |
| 626-24 | 6-32, 8-32, 10-24    | replacement for 623-24      |
| 626-32 | 6-32, 8-32, 10-32    | replacement for 623-32, 626 |

## Six-in-One Tapping Tools



627-20

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.
- Two high-carbon steel taps are secured in reversible holder.

| Cat. No. | Tap Sizes                               | Overall Length  | Weight (lbs.) |
|----------|---|-----------------|---------------|
| 627-20   | 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20 | 7-5/8" (194 mm) | 0.35          |

### Replacement Taps

|        |                      |
|--------|----------------------|
| 626-32 | 10-32, 8-32, 6-32    |
| 628-20 | 10-24, 12-24, 1/4-20 |

## Triple Taps



625-24

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions.
- Each tap size rethreads to next larger size if threads are stripped.

| Cat. No. | Tap Sizes         | Color Code | Overall Length  | Weight (lbs.) |
|----------|-------------------|------------|-----------------|---------------|
| 625-24   | 6-32, 8-32, 10-24 | blue       | 7-1/8" (181 mm) | 0.20          |
| 625-32   | 6-32, 8-32, 10-32 | orange     | 7-1/8" (181 mm) | 0.20          |

### Replacement Taps

|        |                     |
|--------|---------------------|
| 626-24 | for Cat. No. 625-24 |
| 626-32 | for Cat. No. 625-32 |

## Cushion-Grip Scratch Awl



650

- Professional, heavy-duty, hard-pointed awl.
- Scribes metal, starts screw holes, performs a variety of piercing and punching jobs.
- Rigid, chrome-plated, heat-treated, tempered-steel shank has full reinforcing bolster at handle for extra strength and for handle impact reinforcement.
- Internal flanges provide solid shank anchor.
- Cushion-Grip handle allows for greater comfort.

| Cat. No. | Blade Length   | Overall Length  | Weight (lbs.) |
|----------|----------------|-----------------|---------------|
| 650      | 3-1/2" (89 mm) | 7-7/8" (200 mm) | .25           |

**⚠WARNING:** Do NOT hammer on tool.

## Steel Scratch Awl



66385

- One-piece forged-steel blade and bolstered shank.
- Heat treated for long life.
- Well-balanced for top efficiency during use.
- Black finish for rust resistance.

| Cat. No. | Blade Length   | Overall Length | Weight (lbs.) |
|----------|----------------|----------------|---------------|
| 66385    | 3-1/2" (89 mm) | 7" (178 mm)    | .30           |

**⚠WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠WARNING:** Always wear approved eye protection.

**⚠WARNING:** Never use on or near live electrical circuits.

