



BURNDY Catalog Number YAL30T12
UPC Number 78181041721
Description CANLUG-300KCML-SHORT-1/2
Status null

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.52
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Standard
Thickness	0.16
B Length (in)	0.97
Pad Width (in)	1.2
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	300
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Color Code	White
Plated (Yes or No)	Y
Index Number	17
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A-468B
UL Listed	Yes,Y
CSA Certified	Yes,Y
ROHS Compatible	Compliant
UL Recognized	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
 47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services
 47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175