



BURNDY Catalog Number YAL31T12
UPC Number 78181041727
Description CANLG-350KCMIL-SHORT-1/2
Status null

Web Use
BURNDY Product Line

Dimensional

Tongue Angle Straight
Length (in) 2.54
Tongue Type Standard
Barrell Style Chamfered
Bolt Hole Size (in) 0.52
Barrel Type Standard
Thickness 0.18
B Length (in) 0.96
Pad Width (in) 1.29

General

Number of Holes 1

Conductor(s)

Copper Stranded (Range) 350
Copper Solid Size (Range) N/A

Physical

Type of Plating Tin - Electro Plated
Color Code Red
Plated (Yes or No) Y
Index Number 18
Product Material Copper

Approvals / Certifications

Industry Standards UL468A-468B
UL Listed Yes,Y
CSA Certified Yes,Y
ROHS Compatible Compliant
UL Recognized N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday
Phone: 800-346-4175