



## Accessories for 16A – 125A non-fusible disconnect switches Base & DIN rail mounted



OHRS2



OHBS11



OHBS12



OTZS1



OHY7



CXBY68140



SO0327A

OHZX5

### Replacement Knob – mounts directly to switch; no shaft necessary.

UL/NEMA type	Color	For use on :	Length (MM)	Padlockable	Catalog number	List price
1	Black	OT16...40	25	–	CXBY68989	
1	Black	OT63... 80,OT30,60,100	35	–	CXBY68998	
1	Red	OT63-80, OT30-100	40	Yes	OHRS2	
1	Black	OT16 - OT40	–	Yes	OHBS12	
1	Black	OT160	72	–	OHBS13	
1	Black	OT63... 80,OT30,60,100	–	Yes	OHBS2/1	
Metal collar		OT16-OT200	–	–	OTZS2	
Red knob for locking shaft in place **re-use original set screw **		OT160	–	–	CXBY68100	
Set screw ①		OT16- OT100	–	–	FLSWM5X8AY	

(1) Set screw for use with knob or collar, to be ordered separately.  
Red/Yellow handles are available by substituting the OHB prefix with OHY.

### Modular adapter cover – for OT16, OT25, OT40

Item	For use on :	Length (inches)	Padlockable	Catalog number	List price
Adapter cover grey	OT16, OT25, OT40	–	Yes	OHBS7	
Adapter cover yellow	OT16, OT25, OT40	–	Yes	OHYS7	

A padlock can be used with the adapter cover.

### Locking clip – (replacement part)

Description	For use on :	Catalog number	List price
Door mounted switch handle locking clip	OT16, OT25, OT40	CXBY68140	

### Handle support – (for direct mounting on the switch mechanism for OH\_65, 80 handles)

Description	For use on:	Catalog number	List Price
Handle Support	OT160E3	OHZX5	