








Code•Master™ Factory Sealed Strobe Luminaires

Explosionproof, Dust-Ignitionproof

NEC:
 Class I, Division 1 and 2, Groups C, D
 Class I, Division 2, Groups A, B
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 3R, 4X

NEC:
 Suitable for Wet Locations
 Marine Outside Type (Saltwater)

Standard Strobes		Volts	Catalog Number ①③
Pendant — One Hub 3/4" NPT, Rigid Conduit			
		120 Vac	CSSP75120ACCL
		240 Vac	CSSP75240ACCL
		250 Vdc	CSSP75250DCCL
		24 Vdc	CSSP7524DCCL ②
Ceiling — Four Hubs 3/4" NPT, Three Close-Up Plugs, Rigid Conduit			
		120 Vac	CSSC75120ACCL
		240 Vac	CSSC75240ACCL
		250 Vdc	CSSC75250DCCL
		24 Vdc	CSSC7524DCCL ②
Bracket — Four Hubs 3/4" NPT, Three Close-Up Plugs, Rigid Conduit			
		120 Vac	CSSB75120ACCL
		240 Vac	CSSB75240ACCL
		250 Vdc	CSSB75250DCCL
		24 Vdc	CSSB7524DCCL ②
Fixture Unit Only — Less Mounting Hood			
		120 Vac	CSST120ACCL
	10.36 kg (4.7 lb)	240 Vac	CSST240ACCL
		250 Vdc	CSST250DCCL
		24 Vdc	CSST24DCCL ②
	Weight kg (lb)	Hub Size (Inches)	Catalog Number
Pendant Mounting Hood — One Hub 3/4" NPT, Rigid Conduit			
	9.0 (19.84)	3/4	CAP-75
Ceiling Mounting Hood — Four Hubs 3/4" NPT, Three Close-Up Plugs, Rigid Conduit			
	1.8 (3.97)	3/4	CAC-75
Bracket Mounting Hood — Four Hubs 3/4" NPT, Three Close-Up Plugs, Rigid Conduit			
	2.7 (5.95)	3/4	CALB-75

① Add -G suffix for optional guard.

② Diode polarized (current limiter supplied as standard).

③ Catalog numbers shown are supplied with clear lens. To order colored lens, replace last digits of catalog number CL with AM for amber; BL for blue; GR for green; and RE for red.