

## Ratchet Cable Cutters



- Simple, one-hand operation
- Exclusive two-speed ratcheting mechanism adjusts for light/heavy cutting
- Well-suited for tight working spaces
- Blades can be opened mid-cycle
- Available with cushioned handles or with 1000V insulated cushioned handles

CAT. NO.	UPC NO.	DESCRIPTION
45206	45206	Ratchet Cable Cutter (1.5 lbs/.7 kg)
45206I	12680	Ratchet Cable Cutter with Insulated Handles (1.5 lbs/.7 kg)
45207	45207	Ratchet Cable Cutter (2.4 lbs/1.1 kg)
45207I	12681	Ratchet Cable Cutter with Insulated Handles (2.4 lbs/1.1 kg)
45218	45218	<b>R</b> Movable Blade (45206 & 45206I)
45212	45212	<b>R</b> Fixed Blade and Handle (45206)
12526	12526	<b>R</b> Fixed Blade and Handle (45206I)
45211	45211	<b>R</b> Movable Blade (45207 & 45207I)
45228	45228	<b>R</b> Fixed Blade and Handle (45207)
05883	05883	<b>R</b> Fixed Blade and Handle (45207I)

### SPECIFICATIONS

	Copper	Aluminum	Communications Cable
<b>45206 &amp; 45206I</b>			
<b>Maximum Capacity*</b>	600 kcmil (MCM) (300 mm <sup>2</sup> )	600 kcmil (MCM) (300 mm <sup>2</sup> )	1-3/8" (35 mm) dia.
<b>Frequent Use Capacity*</b>	500 kcmil (MCM) (240 mm <sup>2</sup> )	500 kcmil (MCM) (240 mm <sup>2</sup> )	
<b>Length</b>	10" (254 mm)		
<b>Jaw opening</b>	1-7/16" (36.5 mm)		
<b>45207 &amp; 45207I</b>			
<b>Maximum Capacity*</b>	750 kcmil (MCM) (400 mm <sup>2</sup> )	1000 kcmil (MCM) (500 mm <sup>2</sup> )	2" (51 mm) dia.
<b>Frequent Use Capacity*</b>	600 kcmil (MCM) (300 mm <sup>2</sup> )	750 kcmil (MCM) (400 mm <sup>2</sup> )	
<b>Length</b>	11" (279 mm)		
<b>Jaw opening</b>	2" (51 mm)		

## Compact Ratchet Cable Cutters



- Simple, one-hand operation.
- Compact – convenient for working in tight places and stores easily in tool pouches.
- Single-speed ratchet mechanism.
- Blade release allows blades to be opened in mid-cut.
- Heavy-duty blades provide long life.

CAT. NO.	UPC NO.	DESCRIPTION
759	45277	Compact Ratchet Cable Cutter
760	17600	Compact Ratchet Cable Cutter
45282	45282	<b>R</b> Movable Blade (759)
45281	45281	<b>R</b> Fixed Blade (759)
09908	09908	<b>R</b> Movable Blade (760)
09907	09907	<b>R</b> Fixed Blade (760)
45297	45297	<b>R</b> Handle Spring

### SPECIFICATIONS

	Copper	Aluminum	Communications Cable
<b>759</b>			
<b>Maximum Capacity*</b>	500 kcmil (MCM) (240 mm <sup>2</sup> )	750 kcmil (MCM) (400 mm <sup>2</sup> )	1-1/8" dia. (28 mm <sup>2</sup> )
<b>Frequent Use Capacity*</b>	400 kcmil (MCM) (185 mm <sup>2</sup> )	600 kcmil (MCM) (300 mm <sup>2</sup> )	
<b>Length</b>	10-1/2" (262 mm)		
<b>Weight</b>	1.4 lbs. (0.6 kg)		
<b>760</b>			
<b>Maximum Capacity*</b>	1000 kcmil (MCM) (500 mm <sup>2</sup> )	1000 kcmil (MCM) (500 mm <sup>2</sup> )	1-3/4" dia. (42 mm <sup>2</sup> )
<b>Frequent Use Capacity*</b>	750 kcmil (MCM) (400 mm <sup>2</sup> )	1000 kcmil (MCM) (500 mm <sup>2</sup> )	
<b>Length</b>	11-3/4" (298 mm)		
<b>Weight</b>	1.75 lbs. (0.8 kg)		

\*Capacity may be less for compact and compressed cables

**N** = NEW PRODUCT **R** = REPLACEMENT PART **A** = ACCESSORY

Wire & Cable Termination

USA

Tel: 800.435.0786  
Fax: 800.451.2632

CANADA

Tel: 800.435.0786  
Fax: 800.524.2853

INTERNATIONAL

Tel: +1.815.397.7070  
Fax: +1.815.397.9247