

# Wire Strippers/Cutters

## Features:



## Wire Strippers/Cutters

### Additional Features:

- Compact, lightweight wire-stripping and cutting tools.
- Narrow nose fits into tight places.
- Hardened steel with precision ground stripping holes.
- Do not use for cutting steel wire or bolts.




Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight (lbs.)
11045	yellow	6-1/4" (159 mm)	10 – 18 AWG solid (4.0 mm <sup>2</sup> – .75 mm <sup>2</sup> )	.27
11046	red	6-1/4" (159 mm)	16 – 26 AWG stranded (1.0 mm <sup>2</sup> – .14 mm <sup>2</sup> )	.27
11047	yellow	6-1/4" (159 mm)	22 – 30 AWG solid (.34 mm <sup>2</sup> – .05 mm <sup>2</sup> )	.27
11049	red	6-1/4" (159 mm)	8 – 16 AWG stranded (6 mm <sup>2</sup> – 1.0 mm <sup>2</sup> )	.27

## Dual-Wire Stripper/Cutter

### Additional Features:

- Strips two wires in a single motion.
- Paired stripping holes for 14 and 12 AWG solid wire.
- One stripping hole for 10 AWG solid wire.
- Shear-type cutting blades for square, clean cuts.
- Narrow nose fits into tight places.
- Hardened steel with precision ground stripping holes.



Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight (lbs.)
11048	yellow	6-1/4" (159 mm)	10, 12, 14 AWG solid (4.0 mm <sup>2</sup> , 2.5 mm <sup>2</sup> , 1.5 mm <sup>2</sup> )	.27

All dimensions are in inches and (millimeters).

**⚠WARNING:** Never use on or near live electrical circuits.

**⚠WARNING:** NOT insulated. Will NOT protect against electrical shock.

**⚠WARNING:** Always wear approved eye protection.

