

Kits and Accessories

Type P2 Panelboards

Table P2-20 – Standard Enclosures

| Box Height Inches | Catalog Number | | | | |
|----------------------|-------------------------|---------|-------|---------|------------|
| | Type 1 Standard Trim | | | Type 3R | Type 3R/12 |
| | Box | Surface | Flush | | |
| 26 | B26 | S26B | F26B | NR26 | WP26 |
| 32 | B32 | S32B | F32B | NR32 | WP32 |
| 38 | B38 | S38B | F38B | NR38 | WP38 |
| 44 | B44 | S44B | F44B | NR44 | WP44 |
| 50 | B50 | S50B | F50B | NR50 | WP50 |
| 56 | B56 | S56B | F56B | NR56 | WP56 |
| 62 | B62 | S62B | F62B | NR62 | WP62 |
| 68 | B68 | S68B | F68B | NR68 | WP68 |
| 74 | B74 | S74B | F74B | NR74 | WP74 |

Options For Type 1 Trims

Hinged trim – Replace “B” suffix with “H”

Door-in-door – Replace “B” suffix with “D”

Metal card holder – Replace “B” suffix with “M” on standard trim, add “M” suffix on optional trims

Option For 24” Wide Enclosures with Equal Gutter on Both Sides

24” wide with equal gutter on both sides - Add “24” as prefix

Table P2-21 – Breaker Kits and Accessories

| Kit No. | Description | Contents |
|---------|---|---|
| BBKB32 | BL/BQD 6-pole 3” branch breaker kit | Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware |
| BBKNB32 | NGB 6-pole 3” branch breaker kit | Kit contains braker support, interphase barriers, (3) A/C connectors, (1) B-phase connector, hardware |
| BBKED32 | ED 6-pole 3” branch breaker kit | Kit contains breaker support, inter-phase barriers, (3) A/C connectors, (1) B-phase connector, hardware |
| BBKQ1 | QJ branch breaker kit for 2 and 3-pole single mount | Kit to contain all connectors and cover plates necessary to mount both 2 and 3-pole breakers |
| DFK1 | BL, BQD, ED deadfront kit for 1” pole breakers | Center strips 3”, 6”, 9,” 15,” 21” plus mounting hardware |
| DFFP3 | Deadfront filler 3” | 3” empty space filler and hardware |
| DFFP6 | Deadfront filler 6” | 6” empty space filler and hardware |
| BNK2 | Branch neutral (P2) | Three tier lug with mounting hardware to increase neutral capacity |
| P2BK1 | P2 250A max. Bonding Kit | Bonding strap and hardware |
| P2BK2 | P2 400A max. Bonding Kit | Bonding strap and hardware |
| P2BK3 | P2 600A max. Bonding Kit | Bonding strap and hardware |