
PL17 Series

100 A 600 V; Polyphase

Product Specifications

- Conductor range: 6-1/0 AWG
- · Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
- · Supplied with screw type ring




2-1/8 in.


1-3/16 in.



(PL17-INV)



COMBINATION AND UNDERGROUND BOTTOM



Cat. No.	Description	Dimensions (in.)			Weight Each	
		Н	W	D	lb.	kg
7 JAW						
PL17-INV	Overhead, hub opening		8-9/16	5-7/16	12	5.4
PL17-INV-HQ	Overhead, hub opening (Hydro-Québec approved)					
PL17-INTV-HQ	Underground (Hydro-Québec spec)					
PL17-INTCV	Combination overhead-underground	15-5/8				
PL17-INTCV-HQ	Combination overhead-underground (Hydro-Québec approved)	10-0/0				
PL17-V	Overhead, hub opening					
PL17-TV	Underground					
PL17-TCV	Combination overhead-underground					
8 JAW						
PL17-8V	Overhead, hub opening	15.5/0	8-9/16	5-7/16	12	5.4
PL17-8TCV	Combination overhead-underground	15-5/8				
FACTORY INSTALLE	D ACCESSORIES					
Include: -IN	Insulated neutral					

1-1/16 in.

OVERHEAD BOTTOM

1-11/16 in.