



### Description

Non-IC rated housing for use in 2/12 to 6/12 pitch slopes (9° to 27°) • Designed to be installed in non-insulated areas, or where insulation is spaced at least 3" from housing • Juno's Slope Ceiling Down-Lites direct light straight down, providing proper lighting from a sloped surface

### Listings

UL Listed, cUL/CSA certified for through-branch wiring, damp and wet locations • Wet location listed with the 610 trim • Conforms with City of Chicago IP requirements

### Features

- 6" Standard slope housing (oval)
- Oblique angle housing design holds trims flush with the ceiling
- Adjustable socket plate permits lamp to remain perpendicular to floor through entire pitch range
- Medium base porcelain socket with nickel-plated copper screw shell
- Housing is vertically adjustable to accommodate up to a 1" ceiling thickness
- Patented (US Patent D552,969) Real Nail® 3 bar hangers: telescoping system with pre-installed removable nail for easy repositioning of housing in joist construction
  - Integral T-bar mounting feature for secure installation in suspended ceilings
  - Breakaway bars for tight joist spacing
  - Bar hangers may be repositioned 90°
  - Curved foot facilitates alignment with joist bottom
  - Quick-Loc slot and oversized set screw lock fixture in position
- Housing is fully assembled for ease of installation
- Pre-wired junction box with (5) 1/2" and (1) 3/4" knockouts with pryout slots, (4) non-metallic sheathed cable connectors, and ground wire
- Shadow-free, knife-edge trim design blends smoothly into the ceiling
- Angle-cut baffles ensure grooves remain parallel to the floor to provide proper optics
- UL Listed, cUL/CSA certified for through-branch wiring, maximum (8) #12 AWG branch circuit conductors (4 in, 4 out)
- Thermally protected against improper use of lamps
- Lamp wattage ratings and apertures based on trim selection. Trim selection follows IC926 and TC926 Series

### Ordering Information

| Catalog No. | Description                            |
|-------------|--|
| TC926       | 6" Standard slope incandescent housing |

### Dimensions

