HOLE DIA.

HEX SHANK

WEIGHT

# **Nail Eater® Extreme**



- Improved cutting edge provides 30% longer life span.
- Patented new design for improved cutting and cleaner holes.
- · Self-feeding screw point draws bit through wood.
- ٠ Patented Pending, cutting angle design- smoother starts, reduced cutting loads.
- · Made of super tough, heat-treated steel; cuts through nails and provides longer life.
- "Shorty" bits for working in tight places, yet still can go through three abutting 2 x 4s.
- See "Bit Extensions" if more length is required (see page 84).
- P.O.P packaged

### SPECIFICATIONS

Twist Length

	NAIL	<b>EATER</b> <sup>®</sup>	EXTREME	SHORTY
--	------	---------------------------	---------	--------

Overall Length	7-5/8" (193.7 mm)						
Twist Length	5" (127 mm)						
Electrical drill required	61 PTS – 5/8 through 61 PTS - 1, minimum 3/8" drill; All Big Shank, 1/2" drill.						
NAIL EATER® EXTREME							
Overall Length	18" (457.2 mm						

CAT. NO.	UPC NO.	UPC NO.	INCH	MM	INCH	MM	LBS	G
61PTS-5/8	30419	_	5/8	15.9	5/16	7.9	.3	137
61PTS-3/4	30423	_	3/4	19.1	5/16	7.9	.4	182
61PTS-7/8	30427	_	7/8	22.2	5/16	7.9	.5	227
61PTS-1	30429	—	1	25.4	5/16	7.9	.8	363
62PTS-5/8	31788	_	5/8	15.9	7/16	11.1	.3	137
62PTS-11/16	31790	—	11/16	17.5	7/16	11.1	.4	182
62PTS3/4	31792	36640	3/4	19.1	7/16	11.1	.5	227
62PTS-13/16	31794	—	13/16	20.6	7/16	11.1	.5	227
62PTS7/8	31796	36642	7/8	22.2	7/16	11.1	.6	273
62PTS-1	31798	36643	1	25.4	7/16	11.1	.7	318
61/62PTS-1-1/8	30431	—	1-1/8	28.6	7/16	11.1	.9	409
61/62PTS-1-1/4	30433	_	1-1/4	31.8	7/16	11.1	1.1	499

#### NAIL EATER® EXTREME

	POP	BULK	HOLE DIA.		HEX SHANK		WEIGHT	
CAT. NO.	UPC NO.	UPC NO.	INCH	MM	INCH	ММ	LBS	G
66PT-1/2	30915	_	1/2	12.7	5/16	7.9	.7	318
66PT-5/8	30919	—	5/8	15.9	7/16	11.1	.8	363
66PT-11/16	30921	—	11/16	17.5	7/16	11.1	1	454
66PT-3/4	30923	36659	3/4	19.1	7/16	11.1	1.2	545
66PT-13/16	30925	—	13/16	20.6	7/16	11.1	1.2	545
66PT-7/8	30927	36662	7/8	22.2	7/16	11.1	1.5	681
66PT-15/16	30929	_	15/16	23.8	7/16	11.1	1.6	726
66PT-1	30931	36664	1	25.4	7/16	11.1	1.8	817
66PT-1-1/8	30935	_	1/8	28.6	7/16	11.1	2.3	1044
66PT-1-1/4	30937	—	1-1/4	31.8	7/16	11.1	2.8	1270

# 15" (381 mm) **Nail Eater® Extreme Impact Bits**



Quickly bore through creosoted and salt-treated utility poles.

- · Resists wear, eats through nails and staples.
- Self-feeding screw point draws the bit through the wood. •
- 7/16" hex shank to fit impact drivers.
- Available in 18" overall length. •

### NAIL EATER® EXTREME

		HARD	VARE	HOLE DIA.		OVERALL		HEX			
	POP	DIAMETER		DIAMETER		LENGTH		SHANK		WEIGHT	
CAT. NO.	UPC NO.	INCH	ММ	INCH	MM	INCH	ММ	INCH	ММ	LBS	G
37868	37868	9/16	14.3	5/8	15.9	18	457.2	7/16	11.1	0.9	409
37869	37869	11/16	17.5	3/4	19.1	18	457.2	7/16	11.1	1.1	499
37870	37870	13/16	20.6	7/8	22.2	18	457.2	7/16	11.1	1.4	636
37871	37871	15/16	23.8	1	25.4	18	457.2	7/16	11.1	1.5	681