

Power-Assisted Compression Tools

Li 14-Ton Open Crimp Tool

- Rotating head allows maximum flexibility for crimping
- Protective rubber boot on "C" head
- Rapid advance feature decreases crimp time
- Approx. 150 crimps per full battery charge (based on 3/0 AWG cable)

Specifications

- Installing Range:
Up to 900 kcmil copper lugs and splices
Up to 750 kcmil aluminum lugs and splices
- Capacity: Cu #8-900 kcmil, Al #10-750 kcmil
- Output Force: 14-Ton
- Dimensions (L x W x H): 19 in. x 3.5 in. x 10.5 in.
- Battery: 14.4 V DC
- Weight with Battery: 20 lb.



Cat. No.	Description	Pkg. Qty.
TBM14CR-LI	Li 14-Ton open crimp tool	1

Battpac™ TBM15CR-LI Hermetically Sealed 15-Ton Battery-Powered Compression Tool

- Rotating head allows maximum flexibility for crimping
- Protective rubber boot on head
- Rapid advance feature decreases crimp time
- Approx. 150 crimps per full battery charge (based on 3/0 AWG cable)

Specifications

- Installing Range:
Up to 1500 kcmil copper lugs and splices
Up to 1250 kcmil aluminum lugs and splices
- Capacity: Cu #8-1500 kcmil, Al #10-1250 kcmil
- Output Force: 14-Ton
- Dimensions (L x W x H): 21.5 in. x 3.5 in. x 10.5 in.
- Battery: 14.4 V DC
- Weight with Battery: 24 lb.



Cat. No.	Description	Pkg. Qty.
TBM15CR-LI	LI 15-Ton Closed crimp tool	1
15500-TB	Die adaptor for 15500 series dies	