



**BURNDY Catalog Number** YAL32T58  
**UPC Number** 7818104173311  
**Description** CANLUG-400KCML-SHORT-5/8  
**Status** Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.94
Barrell Style	Chamfered
Bolt Hole Size (in)	0.66
Barrel Type	Standard
Thickness	0.19
B Length (in)	1.07
Pad Width (in)	1.40
General	
Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 400 kcmil, 5/8" Stud, Short Barrel, Tin Plated
Conductor(s)	
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	400 kcmil
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Blue
Plated (Yes or No)	Y
Index Number	19
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**  
 47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**  
 47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175