



BURNDY Catalog Number YAL26T38
UPC Number 78181041699
Description CANLUG-2/0 STR-SHORT-3/8
Status null

Web Use
BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	1.91
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.12
B Length (in)	0.73
Pad Width (in)	0.83
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	2/0
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Black
Plated (Yes or No)	Y
Index Number	13
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A-468B
UL Listed	Yes,Y
CSA Certified	Yes,Y
ROHS Compatible	Compliant
UL Recognized	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA
47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services
47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175