



Undercabinet Lighting | Pro-Series Halogen

Low Voltage 1-Lamp, 2-Lamp, 3-Lamp & 4-Lamp Fixtures



Description

The Pro-Series Halogen Series of undercabinet lighting delivers the best color rendering and maximum light output from the whitest light source, halogen lamps. The efficient operation of low voltage lamps, combined with a unique housing/reflector system, reduces mounting surface temperatures to be comparable with xenon fixtures, but with the superior light quality of halogen. Pro-Series Halogen fixtures are optimized for fast, permanent installation, mounting either flush to the backsplash or to the front lip of cabinetry to suit project conditions and homeowner preference.

Listing

UL/C-UL Listed

Features

- 12-volt halogen lamps for optimal color rendering
- Integral reflector spaced away from cabinet bottom maximizes light output while reducing fixture/cabinet contact temperature
- Dimmable with standard ELV type wall box dimmers or integral high/low/off rocker switch
- Slim, 1" extruded aluminum profile
- Hinged lens captured by spring loaded retention bar cannot accidentally fall out
- Modular design for maximum flexibility and quick installation allows up to ten fixtures to plug together using the supplied internal straight connector or optional jumper cords
- Miniature die cast fitting for flexible metal conduit, off-center knock-outs and extra mounting plate for feed-through fixture-to-fixture loop wiring increase installation versatility
- Available in Black, Brushed Bronze, Brushed Silver and Designer White finishes

Finishes



Black



Brushed Bronze



Brushed Silver



Designer White

Ordering Information*

Catalog No.	Description
ULH109-BL	9", 1 Lamp, Black
ULH109-BZ	9", 1 Lamp, Brushed Bronze
ULH109-SL	9", 1 Lamp, Brushed Silver
ULH109-WH	9", 1 Lamp, Designer White
ULH214-BL	14", 2 Lamps, Black
ULH214-BZ	14", 2 Lamps, Brushed Bronze
ULH214-SL	14", 2 Lamps, Brushed Silver
ULH214-WH	14", 2 Lamps, Designer White
ULH322-BL	22", 3 Lamps, Black
ULH322-BZ	22", 3 Lamps, Brushed Bronze
ULH322-SL	22", 3 Lamps, Brushed Silver
ULH322-WH	22", 3 Lamps, Designer White
ULH430-BL	30", 4 Lamps, Black
ULH430-BZ	30", 4 Lamps, Brushed Bronze
ULH430-SL	30", 4 Lamps, Brushed Silver
ULH430-WH	30", 4 Lamps, Designer White

*Fixture includes: T3 12V 20W Bi-pin halogen lamp(s)
Mounting hardware
Electrical connector (ULH-CONN)
Joiner connector

Accessories

Catalog No.	Description	
JC3-8-BL	8" Jumper Cord, Black	
JC3-8-WH	8" Jumper Cord, Designer White	
JC3-17-BL	17" Jumper Cord, Black	
JC3-17-WH	17" Jumper Cord, Designer White	
JC3-26-BL	26" Jumper Cord, Black	
JC3-26-WH	26" Jumper Cord, Designer White	
ULH-CONN	3/8" Miniature Die-Cast Electrical Connector	
ULH-CP-BL	6' Cord & Plug, Black	
ULH-CP-WH	6' Cord & Plug, Designer White	
ULH-DWM-BL	Direct Wire Module, Black	
ULH-DWM-WH	Direct Wire Module, Designer White	

Dimensions

