## **In-Line Fan Kits**

- Kits include all components to install a single exhaust system (except wall control, wire and ducting)
- Each kit includes fan, grille, sleeve with damper and duct clamps
- Model ILFK2502 contains 2 grilles (model CVG6) and a 3-way 6" Y adapter (model FY6)


## Model ILFK2502



## **In-Line Fan Kits**

| Model    | CFM | Ducting |  |
|----------|-----|---------|--|
| ILFK120  | 110 | 4"      |  |
| ILFK130  | 130 | 5"      |  |
| ILFK250  | 250 | 6"      |  |
| ILFK2502 | 250 | 6"      |  |

|          | Α                  | В      | C            |
|----------|--------------------|--------|--------------|
| Model    | <b>Duct Collar</b> | Height | Fan Diameter |
| ILFK120  | 37/8"              | 10"    | 10"          |
| ILFK130  | 47/8"              | 73/4"  | 10"          |
| ILFK250  | 57/8"              | 93/8"  | 12"          |
| ILFK2502 | 57/8"              | 93/8"  | 12"          |





## **Accessories**

| Y Adapters | Size         |  |
|------------|--------------|--|
| FY6        | 6" x 6" x 6" |  |
| FY86       | 8" x 6" x 6" |  |



| Grilles/Intakes | Ducting | Size                  | Notes        |  |
|-----------------|---------|-----------------------|--------------|--|
| CVG4            | 4"      | 6" Dia.               | Round Grille |  |
| CVG6            | 6"      | 7-3/4" Dia            | Round Grille |  |
| Sleeves         | Ducting | Notes                 |              |  |
| CVLD4           | 4"      | Sleeve with Damp      | per          |  |
| CVLD5*          | 5"      | Sleeve with Damper    |              |  |
| CVLD6           | 6"      | Sleeve with Damper    |              |  |
| CVL4            | 4"      | Sleeve without Damper |              |  |
| CVL6            | 6"      | Sleeve without Damper |              |  |

<sup>\*</sup>Use with CVG4.

## **Roof Caps**

## Model 634 Roof Cap\*

- For 3-1/4" x 10" or up to 8" round duct
- · Built-in backdraft damper and bird screen
- Steel baked black enamel finish

#### Model 636 Roof Cap\*

- For 3" or 4" round duct
- Built-in backdraft damper and bird screen
- · Steel baked black enamel finish

## Model 636AL Roof Cap\*

• Same as Model 636, except aluminum natural finish

## Wall Caps

### Model 639 Wall Cap\*

- Spring-loaded backdraft damper
- For 3-1/4" x 10" duct
- Built-in bird screen
- Steel baked black enamel finish



#### Model 649 Wall Cap\*

· Same as Model 639, except aluminum natural finish

#### Model 641 Wall Cap\*

- For 6" round duct
- · Aluminum natural finish
- Built-in backdraft damper & bird screen

#### Model 843BL Wall Cap\*

- For 6" round duct
- Built-in backdraft damper and bird screen
- · Steel baked black enamel finish

#### Model 643 Wall Cap\*

- For 8" round duct

# · Aluminum natural finish

#### Model 885BL Wall Cap\*

- For 3" or 4" round duct
- 3" to 4" round transition included
- · Steel baked black enamel finish
- Spring operated built-in backdraft damper and bird screen

#### Model 885AL Wall Cap\*

- Aluminum finish
- · All other features same as 885BL



#### Model WC650 Wall Cap

- 4" round duct
- Includes rigid through-wall duct collar
- White plastic finish

#### **Transitions**

#### **Model 886 Transition**

• Converts 7" round to 3-1/4" x 10" duct

## **Model 475 Transition**

- Converts 6" round duct to 4" round duct reducer
- Available in 6 Pack (475B)

#### **Model 413 Transition**

• Converts 3-1/4" x 10" duct to 8" round duct



## **Ducting, Elbows, Dampers**

#### Model 839 Elbow

- 90° turn
- For use with 3-1/4" x 10" duct

## Model 97 Damper

• 7" spring-loaded, In-Line damper.



#### Model BP87 Damper

• 7" vertical discharge damper.



#### Model 407 Round Duct

- 7" round duct
- 2' galvanized section

## Model 410 Round Duct

- 10" round duct
- 2' galvanized section


## Model 889

• 3-1/4" x 10" duct

## **Adapter Kits**

#### Model RVK1A

- Complete kit designed to vent kitchen or bath exhaust fan through a slanted roof



• 8' in length

## Model WVK2A\* Flexible Wall Ducting Kit

- Includes white polymeric wall cap
- 4" diameter metal duct connector
- 2 duct clamps
- 4" to 3" reducer
- 5' of 4" flexible aluminum ducting

## **Adapters**

#### Model FY6

Model FY86

• 6" x 6" x 6" Y adapter



## • 8" x 6" x 6" Y adapter

## Sleeves

#### Model CVLD4

• 4" sleeve with damper



## • 5" sleeve with damper

## Model CVLD6

Model CVLD5

• 6" sleeve with damper

## Grilles

#### Model S97011308

- Metal Grille kit—10-1/4" x 10-1/4"
- · Steel baked white enamel finish
- Fits fan models 695, 696N, 690RMTLA and 696MTL

#### Model CVG4

- 4" round grille
- · Backdraft damper sold separately

## Model CVG6

- 6" round grille
- · Backdraft damper sold separately



6" -

## Replacement Filters

### Model 834 Filter

• For 8" fans



#### Model 854 Filter

- Aluminum-mesh grease filter
- For 10" fans



## **Insulated Flexible Duct**

#### Models 804DU, DT6W

- 4" (804DU) or 6" (DT6W) round
- 25' standard length



