



Grounding Strip Kits

- Bonds up to 45 RU per rack
- EIA Universal mounting hole pattern

• Engineered to comply with US and International grounding requirements



Threaded Rail Kit



Cage Nut Rail Kit

Part Number	Part Description	Std. Pkg. Qty.		
Grounding Strip Kits for Threaded Rail Fasteners				
RGS134-1Y	Grounding strip; 78.65" (2m) length; .67" (17mm) width; .05" (1.27mm) thickness; provided with .16 oz. (5cc) of antioxidant, one grounding sticker and three each #12-24 x 1/2" and M6 x 12mm thread-forming screws.	1		
RGS134-10-1Y	Ten grounding strips; 78.65" (2m) length; .67" (17mm) width; .05" (1.27mm) thickness; provided with .16 oz. (5cc) of antioxidant, ten grounding stickers and 30 each #12-24 x 1/2" and M6 x 12mm thread-forming screws.	1		
Grounding Strip	Kits for Cage Nut Rail Fasteners			

Grounding Strip Kits for Cage Nut Rail Fasteners

RGS134B-1	Grounding strip; 78.70" (2m) length; .67" (17mm) width; .05" (1.27mm) thickness; provided with .16 oz. (5cc) of antioxidant, one grounding sticker, three cage nut bonding studs, eight #12-24 bonding nuts and three strip clips.	1
RGS134B-10-1	Ten grounding strips; 78.70" (2m) length; .67" (17mm) width; .05" (1.27mm) thickness; provided with .16 oz. (5cc) of antioxidant, ten grounding stickers, 30 cage nut bonding studs, 80 #12-24 bonding nuts and 30 strip clips.	1



Grounding Busbar Kits

- Provide the common grounding point within the cabinet
- Optimized for installation on 19" racks or cabinets that meet EIA-310
- Can be positioned anywhere on the rack or cabinet
- Available pre-assembled with twenty mounting screws for quick and easy installation
- Engineered to comply with US and International grounding requirements



Part Number	Part Description	Std. Pkg. Qty.		
Grounding Busbar Kits for Threaded Rail Fasteners				
RGRB19Y	Grounding busbar; 19" (483mm) length; tin-plated; fourteen holes arranged for flexibility in mounting; provided with two each #12-24 x 1/2" and M6 x 12mm thread-forming screws.	1		
RGRB19U	Grounding busbar; 19" (483mm) length; tin-plated; twenty holes arranged for flexibility in mounting with twenty #12-24 x 1/2" hex head screws installed; mounting hole sets have 5/8" (15.9mm) spacing; provided with two each #12-24 x 1/2", M6 x 12mm thread-forming screws, and two #12 flat washers for mounting.	1		

Grounding Busbar Kit for Cage Nut Rail Fasteners

RGRB19CN	Grounding busbar; 19" (483mm) length; tin-plated; twenty holes arranged	1
	for flexibility in mounting with twenty #12-24 x 1/2" hex head screws	
	installed; mounting hole sets have 5/8" (15.9mm) spacing; provided with	
	two cage nut bonding studs and four #12-24 bonding nuts.	

About **Panduit**

Copper **Systems**

Fiber **Systems**

D. Faceplates Outlet Frames & Surface **Mount Boxes**

> Keystone Cabling Systems

F. Zone Cabling

Cable Routing Systems

Surface Raceway

Cabinets. Racks & Cable Management Systems

Power Management

> Grounding Bonding

Identification **Products**

Cable Management Accessories

> 0. Part Number Index