



BURNDY Catalog Number YAL252T38
UPC Number 78181041692
Description CANLG-1/0STR-SHORT-3/8X1
Status null

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.74
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.12
B Length (in)	0.72
Pad Width (in)	0.75
E - in	1
General	
Number of Holes	2
Conductor(s)	
Copper Solid Size (Range)	1/0
Copper Stranded (Range)	1/0
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Pink
Plated (Yes or No)	Y
Index Number	12
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A-468B
UL Listed	Yes,Y
CSA Certified	Yes,Y
ROHS Compatible	Compliant
UL Recognized	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA
 47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services
 47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175