

Panelboards

Distributor Stock

Selection

Pricing An Unassembled Panel

400A Max. — 20" Wide x 5.75" Deep

1. Choose the appropriate Interior from the table below.
2. Choose and price the Main Device:
Main Lugs from pages 10-11, Main Breaker Kit from page 10-13 and Main Breakers from Section 6.
3. Choose and price Branch Breakers.
BL, BOD and NGB breakers from Section 6.
4. Choose and price Feed-Thru Lugs or Subfeed Breaker Feed-Thru Lugs from page 10-11, Subfeed Breaker Kit from page 10-11, and Subfeed Breaker from Section 6.



Type P1 Unassembled Panelboards

Convertible Mains — 1 Phase, 3 Wire

120 / 240V

Interiors Only—Less Branch Breakers					Boxes				Fronts			
Total List Price \$	Amperes Rating Mains	Max. No of Poles	Interiors	List Price \$	Height (inches)	Type 1	List Price \$	Type 3R/12 [Ⓞ]	List Price \$	Surface	Flush	List Price \$
836.50	250	18	P1A18MC250A	594.00	32	B32	49.50	WP32	1594.00	S32B	F32B	247.00
975.50		30	P1A30MC250A	742.00	38	B38	49.50	WP38	1594.00	S38B	F38B	247.00
1201.50		42	P1A42MC250A	983.00	44	B44	49.50	WP44	1594.00	S44B	F44B	247.00
1303.00	400	18	P1A18MC400A	924.00	56	B56	101.00	WP56	1737.00	S56B	F56B	362.00
1443.00		30	P1A30MC400A	1074.00	62	B62	101.00	WP62	1737.00	S62B	F62B	362.00
1669.00		42	P1A42MC400A	1314.00	68	B68	101.00	WP68	1737.00	S68B	F68B	362.00
893.50	250	18	P1A18MC250C	655.00	32	B32	49.50	WP32	1594.00	S32B	F32B	247.00
1066.50		30	P1A30MC250C	839.00	38	B38	49.50	WP38	1594.00	S38B	F38B	247.00
1310.50		42	P1A42MC250C	1099.00	44	B44	49.50	WP44	1594.00	S44B	F44B	247.00
1389.00	400	18	P1A18MC400C	1016.00	56	B56	101.00	WP56	1737.00	S56B	F56B	362.00
1562.00		30	P1A30MC400C	1200.00	62	B62	101.00	WP62	1737.00	S62B	F62B	362.00
1806.00		42	P1A42MC400C	1460.00	68	B68	101.00	WP68	1737.00	S68B	F68B	362.00

Convertible Mains — 3 Phase, 4 Wire

208Y / 120V

836.50	250	18	P1X18MC250A	594.00	32	B32	49.50	WP32	1594.00	S32B	F32B	247.00
1068.50		30	P1X30MC250A	841.00	38	B38	49.50	WP38	1594.00	S38B	F38B	247.00
1301.50		42	P1X42MC250A	1089.00	44	B44	49.50	WP44	1594.00	S44B	F44B	247.00
1373.00	400	18	P1X18MC400A	999.00	56	B56	101.00	WP56	1737.00	S56B	F56B	362.00
1604.00		30	P1X30MC400A	1245.00	62	B62	101.00	WP62	1737.00	S62B	F62B	362.00
1838.00		42	P1X42MC400A	1494.00	68	B68	101.00	WP68	1737.00	S68B	F68B	362.00
896.50	250	18	P1X18MC250C	658.00	32	B32	49.50	WP32	1594.00	S32B	F32B	247.00
1152.50		30	P1X30MC250C	931.00	38	B38	49.50	WP38	1594.00	S38B	F38B	247.00
1402.50		42	P1X42MC250C	1197.00	44	B44	49.50	WP44	1594.00	S44B	F44B	247.00
1489.00	400	18	P1X18MC400C	1123.00	56	B56	101.00	WP56	1737.00	S56B	F56B	362.00
1743.00		30	P1X30MC400C	1393.00	62	B62	101.00	WP62	1737.00	S62B	F62B	362.00
1994.00		42	P1X42MC400C	1660.00	68	B68	101.00	WP68	1737.00	S68B	F68B	362.00

Convertible Mains — 3 Phase, 4 Wire

480Y / 277V

836.50	250	18	P1E18MC250A	594.00	32	B32	49.50	WP32	1594.00	S32B	F32B	247.00
1068.50		30	P1E30MC250A	841.00	38	B38	49.50	WP38	1594.00	S38B	F38B	247.00
1301.50		42	P1E42MC250A	1089.00	44	B44	49.50	WP44	1594.00	S44B	F44B	247.00
1373.00	400	18	P1E18MC400A	999.00	46	B56	101.00	WP56	1737.00	S56B	F56B	362.00
1743.00		30	P1E30MC400A	1245.00	62	B62	101.00	WP62	1737.00	S62B	F62B	362.00
1838.00		42	P1E42MC400A	1494.00	68	B68	101.00	WP68	1737.00	S68B	F68B	362.00
896.50	250	18	P1E18MC250C	658.00	32	B32	49.50	WP32	1594.00	S32B	F32B	247.00
1152.50		30	P1E30MC250C	931.00	38	B38	49.50	WP38	1594.00	S38B	F38B	247.00
1402.50		42	P1E42MC250C	1197.00	44	B44	49.50	WP44	1594.00	S44B	F44B	247.00
1489.00	400	18	P1E18MC400C	1123.00	56	B56	101.00	WP56	1737.00	S56B	F56B	362.00
1743.00		30	P1E30MC400C	1393.00	62	B62	101.00	WP62	1737.00	S62B	F62B	362.00
1994.00		42	P1E42MC400C	1660.00	68	B68	101.00	WP68	1737.00	S68B	F68B	362.00

ⓄFront included in NEMA 3R Box.