


WORKSTATION POWER SOLUTIONS



Work Station Power Solutions are point-of-use, plug-in outlet centers available with and without surge suppression.

CODE REFERENCE

cULus Listed: File E66421 Guide XYBS, XUHT, VZCA

Surge Suppression Specifications

Sentrex® High Performance Surge Specifications

Surge Protection Circuitry	3 Element, 3-Stage Hybrid Circuit
Maximum Surge Current	56,000 Amps (32,000 Amps L-N, 12,000 Amps L-G, 12,000 Amps N-G)
Noise Reduction	+50dB
Response Time	Less than 1 nanosecond

NOTE: See the Joule explanation located on the Cabinet Power Solutions page 626.

Perma-Power® Computer Grade Surge Specifications

	Surge Protection Circuitry	Single Stage
	Maximum Surge Current	36,000 Amps (12,000 Amps L-N, 12,000 Amps L-G, 12,000 Amps N-G)
	Noise Reduction	+35dB
	Response Time	Less than 1 nanosecond


Mounting Information

MOUNTING TYPES

Each Plug-In Outlet Center unit has one of three different mounting types. Each mounting method has been designed to optimize the performance of the product. Complete mounting hardware and installation instructions are included with every unit.


Snap-On/Slide-Off

Mount unit in any position. Catalog No. 8004 includes two aluminum mounting clips that snap onto mounting rails on the back of the unit. Screws also included. Used for all units with 2" [51mm] aluminum housing.



Keyhole Mounting

Mount unit in almost any position. Screws not included. Available on all plastic units and units with 3 1/2" [89mm] aluminum housing.



Spring Clip Mounting

Mount unit in any position. Catalog No. 8002 includes two spring steel mounting clips that snap onto the unit. Screws also included. Used for all units with 1 1/2" [38mm] narrow aluminum housing.





COLOR OPTIONS



Workstation Power Solutions Plug-In Outlet Center Units Part Number descriptions indicate available color options.

WORKSTATION POWER SOLUTIONS

Ordering Information

Work Station Power Solutions - Power Only Plug-In Outlet Center Units Ordering Information (continued)

UL218BC, UL218BD

Plug-In Outlet Center Units



Eight outlets, rugged gray aluminum housing, 15A, lighted switch. 6' [1.8m] (UL218BC) or 15' [4.6m] (UL218BD) 14/3 SJT black cord with NEMA5-15 plug. Length 15" [381mm]. Receptacle center-to-center 1 1/4" [32mm]. Snapon, slide-off mounting.

UL210BC, UL210BD

Plug-In Outlet Center Units



Ten outlets, rugged gray aluminum housing, 15A, lighted switch. 6' [1.8m] (UL210BC) or 15' [4.6m] (UL210BD) 14/3 SJT black cord with NEMA5-15 plug. Length 13" [330mm], width 3 1/2" [89mm]. Receptacle center-to-center 1 15/16" [49mm]. Snap-on, slide-off mounting.

R610, R612 Plug-In Outlet Center Units



Six outlets, putty white aluminum housing, 15A, lighted switch. 6' [1.8m] [R610] or 15' [4.6m] [R612] 14/3 SJT putty white cord with NEMA5-15 plug. Length 12 1/4" [311mm]. Receptacle center-to-center 1 1/4" [32mm]. Snapon, slide-off mounting.

P6, P6-15 Plug-In Outlet Center Units



Six outlets, putty white impact-resistant polymeric housing, 15A, lighted switch, 6' [1.8m] (P6) or 15' [4.6m] (P6-15) 14/3 SJT putty white cord with NEMA5-15 plug. Length 12" [305mm]. Receptacle center-to-center 1 1/4" [32mm]. Keyhole mounting.

UL1090BC, UL1090BD

Plug-In Outlet Center Units



Four outlets, rugged gray aluminum housing, 15A, receptacles rotated 90° and spaced to accommodate transformers. 6' [1.8m] (UL1090BC) or 15' [4.6m] (UL1090BD) 14/3 SJT black cord with NEMA5-15 plug. Length 16" [406mm]. Receptacle center-to-center 3" [76mm]. Snap-on, slide-off mounting.

UL209BC, UL209BD

Plug-In Outlet Center Units



Eight individually switched outlets, lighted on/off switch, putty white finish aluminum housing, 15A. 6' [1.8m] (UL209BC) or 15' [4.6m] (UL209BD) 14/3 SJT black cord with NEMA5-15 plug. Length 13" [330mm], width 3 1/2" [89mm]. Receptacle center-to-center 1 5/16" [33mm]. Snap-on, slide-off mounting.

UL215BC, UL215BD

Plug-In Outlet Center Units



Four individually switched outlets, lighted on/off switch, rugged gray aluminum housing, 15A. 6' [1.8m] (UL215BC) or 15' [4.6m] (UL215BD) 14/3 SJT black cord with NEMA5-15 plug. Length 13" [330mm], width 2" [51mm]. Receptacle center-to-center 2 1/8" [54mm]. Snap-on, slide-off mounting.

ULB420-6, ULB420-15

Plug-In Outlet Center Units



Four 20A, 120V, 60Hz, 2500 watt outlets, lighted switch, putty white aluminum housing, 6' [1.8m] (ULB420-6) or 15' [4.6m] (ULB420-15) 12/3 SJT black cord with NEMA5-15 plug. Length 10 3/4" [273mm]. Receptacle center-to-center 1 1/2" [38mm]. Snap-on, slide-off mounting.

ULB620-6, ULB620-15

Plug-In Outlet Center Units



Six 20A, 120V, 60Hz, 2500 watt outlets, lighted switch, putty white aluminum housing, 6' [1.8m] (ULB620-6) or 15' [4.6m] (ULB620-15) 12/3 SJT black cord with NEMA5-15 plug. Length 13 1/4" [337mm]. Receptacle center-to-center 1 1/2" [38mm]. Snap-on, slide-off mounting.