




Standard Liquid Tight – Female Hub Adapter

Cat. No.	Conduit Size	Dimensions (in.)	
		A	B
5271†	3/8"	1 1/2"	1 1/16"
5272†	1/2"	1 3/8"	1 1/4"
5273†	3/4"	1 7/8"	1 1/2"
5274†	1"	1 7/8"	2 1/8"
5275†	1 1/4"	2 3/8"	2 1/2"

† U.L. Listed as grounding means under NEC 351-7.



90° Angle Connectors

Insulated	Cat. No.		Hub Size	Conduit Size	Dimensions (in.)		
	Non-Insulated	Aluminum			A	B	C
5351	5251	5251AL	1/2"	3/8"	1 5/8"	1 3/8"	9/16"
5352	5252	5252AL	1/2"	1/2"	1 3/8"	1 1/4"	9/16"
5353	5253	5253AL	3/4"	3/4"	1 7/8"	1 3/4"	9/16"
5354	5254	5254AL	1"	1"	1 7/8"	2 3/16"	3/4"
5355	5255	5255AL	1 1/4"	1 1/4"	2 3/8"	2 3/4"	13/16"
5356	5256	5256AL	1 1/2"	1 1/2"	2 3/8"	2 9/16"	13/16"
5357	5257	5257AL	2"	2"	3 1/4"	3 7/16"	7/8"
5358	5258	–	2 1/2"	2 1/2"	3 3/4"	8 7/16"	1"
5359	5259	–	3"	3"	4 1/2"	10 1/4"	1"
5360	5260	–	4"	4"	5 1/2"	12 5/8"	1 1/8"

* Suitable for hazardous locations use in Class I, Div. 2; Class II, Div. 1 and 2; Class III, Div. 1 and 2, where general purpose equipment is specifically permitted per NEC Section 500-2(a).

** 3/8" Conduit Fitting has 1/2" hub.

† U.L. Listed as grounding means under NEC 351-7.

‡ Not U.L. Listed.


Note: U.L. Listed liquidtight; and CSA Certified watertight.

Available with DURA-PLATE® Finish.

U.L. File No. E-23018

CSA File No. 2884

For Wiremesh Grips refer to pages A119, A154.



Prevents severe conduit bends and pullout.

Wiremesh Grips for Liquidtight Fittings

Cat. No.	Conduit Size	Liquidtight Connectors			90° Chase	Chase	Adapter
		Straight	45°	90°			
WMG-LT1	3/8"	5331	5341	5351	5361	5371	5271
WMG-LT2	1/2"	5332	5342	5352	5362	5372	5272
WMG-LT3	3/4"	5333	5343	5353	5363	5373	5273
WMG-LT4	1"	5334	5344	5354	5364	5374	5274
WMG-LT5	1 1/4"	5335	5345	5355	5365	–	5275
WMG-LT6	1 1/2"	5336	5346	5356	5366	–	5276
WMG-LT7	2"	5337	5347	5357	5367	–	5277
WMG-LT8	2 1/2"	5338	5348	5358	5368	–	5278
WMG-LT9	3"	5339	5349	5359	5369	–	5279
WMG-LT10	4"	5340	5350	5360	5370	–	5282

Order wiremesh grip separately: no need to duplicate inventory.

U.L. File No. E23018

CSA File No. 2884 & 4484