E-Z-Ground® Grounding Connectors

Provides a permanent, reliable connection.

Ground Clamp

- · Crimps to cable
- Clamps to ground rod and rebar
- Uses standard Color-Keyed® hand and hydraulic tools
- Color coded for easy installation die selection
- Made from high-conductivity wrought copper
- Furnished with stainless steel hardware, 1/4" washers, bolts and nuts
- UL467 approved for direct burial







CAT. NO.	WIRE SIZE	GROUND ROD DIAMETER (IN.)	REBAR # (IN.)	BOLT Size (In.)	DIE CODE
CC2C-45R	#2-#3 AWG	½ or %	4/5	1/4	33-BROWN
CC1C-45R	#1 AWG	½ or 5/8	4/5	1/4	37-GREEN
CC10C-56R	1/0 AWG	5% or 33/4	5/6	3/8	42-PINK
CC20C-56R	2/0 AWG	5% or 33/4	5/6	3/8	45-BLACK
CC40C-56R	4/0 AWG	5/8 or 3/4	5/6	3/8	54-PURPLE

UL467 - Approved for direct burial.

Terminate or connect continuous runs of copper cable to flat surfaces.

Flat-Surface Ground Clamp

- Captivated "keeper bar" design extends cable range and helps hold cable prior to crimping, facilitating installation
- Saddles marked with conductor size and die code
- Conductor can be assembled to saddle with standard dies and hydraulic tools
- Made from high-conductivity cast copper









	WIRE	BOLT	DIE CODE	UNIT	STD.	WT. PER	HEX DIE		INCHES				
CAT. NO.	RANGE	HOLE	NO.*	QUAN.	PKG.	100	CAT. NO.	DIE CODE NO.	L1	L2	D	C	н
53055FL	1/0-2/0 AWG	3/8"	66	2	10	75	15534*	66	43/32	3 ²¹ / ₃₂	9/32	1%	1
53065FL	4/0 AWG-250 kcmil	3/8"	87H	2	10	112	15506**	87H	41/2	43/32	5/16	13/8	1

^{*} TM14M, 13100A, TBM15I with hex crimp dies.

Bond copper conductors to steel or aluminum fence post or top rail of round fence posts.

Grid-to-Fence Ground Clamp

- · Provide quick, dependable installation at low installed cost
- Use no incendiary materials
- Body made from cast copper alloy with steel U-bolt



CAT. NO.	GROUND Cable Range	DIE CODE	STEEL & ALUMINUM Line Post Range (In.)
FG2040R2	2/0-3/0-4/0 Str.	76	2
FG2040R25	2/0-3/0-4/0 Str.	76	21/2
FG2040R3	2/0-3/0-4/0 Str.	76	3
FG210R2	#2-#1-1/0 Sol. or Str.	66	2
FG210R25	#2-#1-1/0 Sol. or Str.	66	2½
FG210R3	#2-#1-1/0 Sol. or Str.	66	3

Install with hydraulic tooling with hex crimp dies.





^{**} TBM15I with hex crimp dies only.