

Armoured Cable / Flexible Conduit

Accessories



CI5153



CI5154



Cat. No.	Trade Size (in.)		Clamping Range (in.)	
	EMT	Flex.	Min.	Max.
E.M.T / Flex. Couplings (Zinc Alloy)				
CI5153	1/2	3/8	0.17	0.63
CI5154		1/2	0.75	0.95

CI0 / CI5

CIS-3 / CIS-4



Cat. No.	Dimensions (in.)		Hole Size (in.)	Suggested Application AC90 (BX)	Flex. Conduit (in.)
	H	W			
Cable Straps (Aluminum)					
CI0	0.44	0.63	3/16	14/2	—
CI1	0.50	0.56	3/16	12/2-10/2; 14/3-12/3; 14/4	5/16
CI2	0.50	0.63	3/16	10/3; 12/4	3/8
CI3	0.57	0.68	3/16	10/2; 10/3; 12/4	—
CI4	0.81	1.06	3/16	6/2; 6/3; 8/4	1/2
CI5	1.06	1.25	7/32	4/2-2/2; 4/3-2/3; 6/4-4/4	3/4
Cable Staples (Galvanized Steel)					
CIS-3	0.49	0.70	—	14/2-12/2; 14/3-12/3	5/16
CIS-4	0.76	0.86		14/2-8/2; 14/3-8/3; 14/4-10/4	3/8, 7/16

CI38



Cat. No.	Trade Size (in.)	Max. Flex. Conduit Dia. (in.)	Hole Size (in.)
Flexible Conduit Strap (Galvanized Steel)			
CI38	3/8	0.61	3/16

CI7538



Cat. No.	Max. Flex. Conduit Dia. (in.)	Hole Size (in.)
One Hole Double Sided Strap (Galvanized Steel)		
CI7538*	1.05	3/16

*Any combination of 3/8 in., 1/2 in. and 3/4 in.
EMT, rigid conduit, flexible conduit or teck cables