

## **Clear Lube**<sup>™</sup>



- Designed for use within electrical or datacom cable pulls.
- Clear and colorless for quick, easy clean-up.
- · Environmentally safe, non-hazardous, non-toxic and non-corrosive.
- Easy to apply either by hand, brush or pump.
- · Polymer base with no silicon additives.
- Three-year shelf life with no deterioration in lubricant.

| CAT. NO. | UPC NO. | DESCRIPTION                                      |
|----------|---------|--|
| CLR-Q    | 10437   | Clear Lube pulling lubricant, 1 quart (.95 l)    |
| CLR-1    | 10438   | Clear Lube pulling lubricant, 1 gallon (3.79 l)  |
| CLR-5    | 10439   | Clear Lube pulling lubricant, 5 gallon (18.93 l) |

## SPECIFICATIONS

| Weight      | CLR-Q - 2.3 lbs. (1.0 kg)   |  |  |  |  |  |
|-------------|-----------------------------|--|--|--|--|--|
|             | CLR-1 - 7.6 lbs. (3.5 kg)   |  |  |  |  |  |
|             | CLR-5 - 44.8 lbs. (20.4 kg) |  |  |  |  |  |
| Viscosity   | 10,000 - 20,000 CPS         |  |  |  |  |  |
| PH Range    | 6.0 - 8.0                   |  |  |  |  |  |
| Average COF | 0.26                        |  |  |  |  |  |

## SWABS, BRUSHES, MANDRELS

Lube Spreader Swab



- Spreads a coat of wire lubricant in duct before installation of cable.
- Cleans mud, dirt, and light debris from duct before pulling.
- Tapered shape permits bi-directional use.
- Will not damage inner walls of duct.

|          |         |           |      | MAXIMUM   |       | maximum<br>Rated |      |        |      |
|----------|---------|-----------|------|-----------|-------|------------------|------|--------|------|
|          |         | DUCT SIZE |      | DISK SIZE |       | CAPACITY         |      | WEIGHT |      |
| CAT. NO. | UPC NO. | INCH      | ММ   | INCH      | ММ    | LBS.             | KN   | LBS.   | KG   |
| 16854    | 16854   | 2         | 50.8 | 1.75      | 44.5  | 4800             | 21.3 | .5     | .23  |
| 16856    | 16856   | 2.5       | 63.5 | 2.25      | 57.2  | 4800             | 21.3 | .6     | .27  |
| 16857    | 16857   | 3         | 76.2 | 2.75      | 69.9  | 4800             | 21.3 | 1.5    | .68  |
| 16858    | 16858   | 3.5       | 88.9 | 3.25      | 82.6  | 4800             | 21.3 | 2.0    | .91  |
| 16859    | 16859   | 4         | 102  | 3.75      | 95.3  | 4800             | 21.3 | 2.5    | 1.13 |
| 17370    | 17370   | 5         | 127  | 4.75      | 120.7 | 4800             | 21.3 | 3.5    | 1.59 |
| 17571    | 17571   | 6         | 152  | 5.75      | 146.1 | 4800             | 21.3 | 4.0    | 1.81 |