

Plastic In-Use Weatherproof Covers

Double-Gang Models

Plastic In-Use Weatherproof Covers are easy to install and include a gasket, mounting screws, base, cover assembly, and inserts to meet the needs of a variety of applications.

Applications

- Industrial • Commercial • Manufacturing • Residential
- Agricultural • Signage • Athletic Fields

Features

- Complies with 2014 NEC Article 314.15 for damp and wet locations
- Exceeds CEC Article 26-702
- UL Certified for Type 3R outdoor enclosures
- Meets requirements for cold impact testing: -60° F (-51° C)
- Heavy-duty UV stabilized polycarbonate cover, mounting base and inserts
- 1/8" (3 mm) thick neoprene gasket with slits for mounting screws
- Six inserts provided with all models that allow each model to meet multiple installations (up to 70 configurations)
- Max cord size: (2) #14 AWG or (1) #12 AWG;
WP1250 (2) #14 AWG or (1) #10 AWG
- Warranty: 1-year limited



Double-Gang - Vertical Hinge

Model #	Color	Depth	Flexi-Guard Inserts
WP1220C	Clear	2 1/4" (57 mm)	WP217
WP1220GC	Gray	2 1/4" (57 mm)	WP217
WP1220WC	White	2 1/4" (57 mm)	WP217
WP1230C	Clear	3 1/8" (79 mm)	WP217
WP1250C	Clear	4 3/4" (121 mm)	WP217

Accessories (detailed on pg 122)

Double-Gang Insert	WP217
--------------------	-------



WP1250

Dimensions

