Mounting Bases for Heavy-Duty Applications

Designed for indoor or outdoor use and heavy-duty applications.

Framing Channel Clamp

- · Quick and easy to install on existing metal framing channel
- Installs with a push and twist
- Smooth design protects cable insulation
- Takes range of cable diameters

When fastening wire bundles, cables or hoses to framing channels, you can cut costs considerably by using the Ty-Rap® cable clamp. It's made of smooth, weather-resistant nylon and designed to protect cable insulation and hoses from wear or damage, which can occur with metal clamps. The clamp may be used for both indoor or outdoor applications. It quickly installs in the framing channel with a simple push and twist. It requires no screws, nuts or tools. The clamp fits all 11/2" and 1%" channels regardless of channel depth.









STD. PKG. CHANNEL CAT. NO. SIZE (IN.)		MAXIMUM TIE WIDTH ACCOM.	STD. PKG. QTY.
TC5363X	1½ & 1%	.301/7.65	50


· Made from high-impact weather-resistant black nylon For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).

Specially designed head is range-taking.

Ty-Rap® Mounting Base for Masonry and Brick Surfaces



- Quick, easy installation without cumbersome adhesives or epoxies
- Provides a quick, easy and dependable means of attaching cable and wires to masonry surfaces
- Installs by tapping it into a drilled hole
- · It's immediately ready to accept a cable tie and wire bundle no tedious surface preparation; no waiting for adhesives to set



- Replaces a variety of anchors, clamps, screws and adhesives
- Designed for both indoor and outdoor applications
- · Only two sizes to stock reduces inventory

STD. PKG. CAT. NO.	HOLE Size in Masonry	MAXIMUM TIE WIDTH ACCOM.	STD. PKG. QTY.
TC5358	1/4	.190/4.83	100
TC5359	¾	.500/12.70	50

· Made of a special impact and ultraviolet-resistant black nylon For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).

Weather-resistant!

Ty-Rap® Mounting Base for Lashing Tie

- For use with lashing ties up to .500" width (i.e. TY5409)
- · High impact

STD. PKG. CAT. NO.	MOUNTING METHOD	TIE WIDTH ACCOM.	MAXIMUM WIDTH IN./MM.	LENGTH IN./MM.	STD. PKG. QTY.
TC5355	#8 screw	.500/12.70	.750/19.05	1.750/44.45	25
TC5356	#10 screw	.500/12.70	.750/19.05	1.750/44.45	25
TC5357	1/4" screw	.500/12.70	.750/19.05	1.750/44.45	25

· Black nylon construction

For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).



