# SWITCHES

## Manual Controllers 60A NEMA 3R Manual Controller 20 & 30A 1ø





#### **Features**

- High horsepower rating, up to 3 HP for heavy duty applications.
- Compact design provides ease of installation.
- Box lug terminals.
- Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life.
- Made in USA.
- Wire pockets and thick wall arc barriers.
- Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements.
- Type 3R enclosure has 2-1/2", 3/4" and 1" concentric knockouts on bottom.
- Accepts #4 AWG.
- cULus listed.
- Slotted opening on enclosure allows for lock-out, tag-out functionality

78	36	3	R

		RATING				
CATALOG NUMBER	DESCRIPTION	A.	VAC	HP	VAC	
DOUBLE POLE MANUAL MOTOR CONTROLLER						
7862R	Double Pole AC Manual Motor Controller in a NEMA 3R Enclosure	60	600 max.	3 5 15 15	120 240 480 600	
7862	Double Pole AC Manual Motor Controller	60	600 max	Same as 7862R		
THREE POLE MANUAL MOTOR CONTROLLER						
7863R	Three Pole AC Manual Motor Controller in a NEMA 3R Enclosure	60	600 max.	5 10 20 30	120 240 480 600	
7863	Three Pole AC Manual Motor Controller	60	600 max	Same as 7863R		
NEMA 3R ENCLOSURE						
7860	NEMA 3R Enclosure for 7862 & 7863					





### Horsepower Rated Switches

#### Features

- Oversize silver contacts for long life and better heat dissipation.
- Single phase switches are side wired with #14 AWG #10 AWG copper or copperclad conductors.
- Shallow design for ease of installation.
  2-3/4" hubs (HP30EX).
- RATING CATALOG NUMBER DESCRIPTION ΗP A. VAC VAC **DOUBLE POLE, SINGLE PHASE** PS20AC2HP Double Pole, Single Phase AC Manual 120/277 20 120 1 Motor Starting Switch 2 240 (No overload protection) PS30AC2HP Double Pole, Single Phase AC 30 120/277 1 120 Manual Motor Starting Switch 240 2 (No overload protection) HP30EX PS30AC2HP in a NEMA 7 & 9 Same as Enclosure for Hazardous Locations PS30AC2HP Class I - Groups C, D; Class II - Groups E, F, G
- 1.320"-3.281" 2.375" 2.196" PS20AC2HP PS30AC2HP

## DEVICES & WALL PLATES Color Selection Chart

## **Devices & Plastic Wall Plate Colors**



See specific device and wall plate catalog charts for particular color availabilities.

#### Metal Wall Plates Metal Finish



## **Custom Metal Wall Plates Paint Finish Colors**

To order custom metal wall plates, see Pages P-41 - P-45. For additional colors consult factory.

SWITCHES