

Cover for 30A Turnlok® Watertight Receptacle

6800



2.38" diameter opening to accommodate a 30A Turnlok watertight receptacle.



features & benefits

- Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.
- Stainless steel mounting screws also resist corrosion.
- Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).
- Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.
- WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.
- Covers fit all competitive inlets and outlets.
- Pre-attached gaskets for easy installation and tight seal to panel or weatherproof box -- with no misaligned or collapsed gaskets.
- Tamper-proof hinge features permanent, locked-in pins for added security.

specifications

General Info

Color: Black

Type: Covers

Features: Watertight

Duty: Heavy Duty

Special Features: Weatherproof

Listing Agencies/Third Party Information

CSA Standard: Yes
cULus: Yes
UL Listing No: Yes

Dimensions

Height U S: 4.60"
Width U S: 3.00"

Technical Information

Material: Plastic
Capacity: 30A Receptacle

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA
Buy American Act Status: Buy American Act Compliant