

Circuit Breakers

Type QP with INSTA-WIRE

Selection

1-Pole Plug-In (120V AC) ^{①⑤}

Continuous Current Rating @ 40° C	Type QP		Type QPH		Type HQP	
	10,000A IR		22,000A IR		65,000A IR	
	Catalog Number	List Price \$	Catalog Number	List Price \$	Catalog Number	List Price \$
10	Q110 [®]	31.50	—	—	—	—
15	Q115 [®]	31.50	Q115H [®]	63.00	Q115HH [®]	117.00
20	Q120 [®]	31.50	Q120H [®]	63.00	Q120HH [®]	117.00
25	Q125	31.50	Q125H■	63.00	Q125HH■	117.00
30	Q130	31.50	Q130H	69.00	Q130HH■	136.00
35	Q135■	31.50	Q135H■	69.00	Q135HH■	136.00
40	Q140	31.50	Q140H	69.00	Q140HH■	136.00
45	Q145■	31.50	Q145H■	69.00	Q145HH■	136.00
50	Q150	31.50	Q150H	69.00	Q150HH■	136.00
60	Q160	31.50	Q160H■	69.00	Q160HH■	136.00
70	Q170	66.00	Q170H■	89.00	Q170HH■	170.00



2-Pole Plug-In (Common-Trip 120/240V AC) ^{①⑥}

10	Q210 [®]	68.00	—	—	—	—
15	Q215	68.00	Q215H	140.00	Q215HH	298.00
20	Q220	68.00	Q220H	140.00	Q220HH	298.00
25	Q225	68.00	Q225H■	140.00	Q225HH■	298.00
30	Q230	68.00	Q230H	140.00	Q230HH	298.00
35	Q235	68.00	Q235H■	140.00	Q235HH■	298.00
40	Q240	68.00	Q240H	140.00	Q240HH■	318.00
45	Q245	68.00	Q245H■	140.00	Q245HH■	318.00
50	Q250	68.00	Q250H	140.00	Q250HH	318.00
60	Q260	68.00	Q260H	140.00	Q260HH	318.00
70	Q270	138.00	Q270H	225.00	Q270HH	531.00
80	Q280	200.00	Q280H■	314.00	Q280HH■	656.00
90	Q290	200.00	Q290H	314.00	Q290HH■	656.00
100	Q2100	200.00	Q2100H	314.00	Q2100HH	656.00
110	Q2110	412.00	Q2110H	1074.00	Q2110HH■	2169.00
125	Q2125	412.00	Q2125H	1074.00	Q2125HH	2169.00



2-Pole Plug-In (Common-Trip 240V AC) ^{①④⑤}

15	Q215R	203.00	—	—	—	—
20	Q220R	203.00	—	—	—	—
30	Q230R	203.00	—	—	—	—
40	Q240R	203.00	—	—	—	—
50	Q250R	203.00	—	—	—	—
60	Q260R	203.00	—	—	—	—
70	Q270R	225.00	—	—	—	—
100	Q2100R■	314.00	—	—	—	—

3-Pole Plug-In (Common-Trip 240V AC) ^{①⑦}

10	Q310 [®]	250.00	—	—	—	—
15	Q315	241.00	Q315H	376.00	Q315HH■	502.00
20	Q320	241.00	Q320H	376.00	Q320HH	502.00
25	Q325	241.00	Q325H■	376.00	Q325HH■	456.00
30	Q330	241.00	Q330H	376.00	Q330HH	502.00
35	Q335	241.00	Q335H■	341.00	Q335HH■	456.00
40	Q340	241.00	Q340H	376.00	Q340HH	586.00
45	Q345	241.00	Q345H■	376.00	Q345HH■	456.00
50	Q350	241.00	Q350H	376.00	Q350HH	586.00
60	Q360	241.00	Q360H	476.00	Q360HH	629.00
70	Q370	302.00	Q370H	476.00	Q370HH■	629.00
80	Q380	362.00	Q380H	533.00	Q380HH■	705.00
90	Q390	362.00	Q390H	533.00	Q390HH■	705.00
100	Q3100	362.00	Q3100H	533.00	Q3100HH	705.00



QP / QPH / HQP Internal Accessories

Control Voltage AC	Catalog Number	Field/Factory Installed	List Price \$
120V Shunt Trip	add suffix ...00S01■	Factory	134.00 (adder)
24V Shunt Trip	add suffix ...00S07■	Factory	134.00 (adder)
120V Auxiliary Switch	add suffix ...01■ [®]	Factory	74.00 (adder)
3-Pole Padlocking Device	ECQLD3	Field	93.00
Handle Block	ECHBD1	Field	8.70

Modifications

Description	Catalog Number	List Price \$
400 Hz Calibration	add suffix ...Y [®]	7.50 (adder)
415V 50Hz Calibration	add suffix ...E [®]	No adder
Marine 50°C Ambient Calibration	add suffix ...M	No adder
Fungus Proofing	add suffix ...F	10.00 (adder per pole)

■ Built to order. Allow 2-3 weeks for delivery

① UL Listed for use with 60/75" wire through 125 amps, HACR rated.

② 1A and 1B contacts

③ UL Listed for frequent switching applications (SWD).

120V AC Fluorescent Lighting.

④ UL Listed for use on 3 phase grounded "B" systems — 10,000 for this application.

⑤ Shipped 12 per sleeve

⑥ Shipped 6 per sleeve

⑦ Shipped 4 per sleeve

⑧ UL Listed 5 KA IR

⑨ Not UL Listed

⑩ 1 & 2 Poles only

⑪ Type QPA