Quick Draw® Hydraulic Punch Driver and Kits



STEEL CAPACITIES FOR CONDUIT SIZES

The Quick Draw[®], Quick Draw 90[®], and Quick Draw[®] Flex feature:

- Compact, lightweight design for portability and fast, easy one-person operation.
- Develops 8 tons of hydraulic force for easy punching, even in 10-gauge stainless steel, depending on individual punch capacities.
- Quick Draw[®] is perfect for fast, straight-on front panel punching.
- Quick Draw 90[®]'s right angle driver head rotates over 180 degrees for maximum flexibility in tight working areas.
- Quick Draw[®] Flex allows unlimited driver orientation to simplify access to work area.
- Can be used with non-round punches within the capacity of the tool (adapter may be required).
- U.S. Patent #6,772,521.

 U.S. Pat 	tent #6,77	2,521.	WEIGHT		
CAT. NO.	UPC NO.	DESCRIPTION	LBS.	KG.	
7704SB	10475	Quick Draw [®] Flex Driver, 2 Draw Studs, 1 Adapter, 1	12.1	5.5	
7706SB	10476	Spacer and Case Standard – Quick Draw [®] Flex Driver, 1/2" through 2" Slug-Buster [®] Conduit Size Punches and Dies, 2 Draw Studs, 1 Adapter, 1 Spacer and Case	17.3	7.9	
7804SB	34292	Quick Draw [®] Driver, 2 Draw Studs, 1 Adapter, 1 Spacer and Case	10	4.5	
7806SB	34293	Standard – Quick Draw [®] Driver, 1/2" through 2" Slug-Buster [®] Conduit Size Punches and Dies 2 Draw Studs, 1 Adapter, 1 Spacer and Case	14	6.4	
7804E	34291	Metric – Quick Draw [®] Driver, 2 Draw Studs, 1 Adapter, 1 Spacer and Case	9.4	4.3	
7804ESB	35611	Metric – Quick Draw [®] Driver, Slug-Buster [®] Pg Punches and Dies 15.2 mm through 30.5 mm, 2 Draw Studs, 1 Adapter, 1 Spacer and Case	10.3	4.7	
7804IS0	35614	Metric – Quick Draw [®] Driver, Slug-Buster [®] ISO Punches and Dies 16.2 mm through 40.5 mm, 2 Draw Studs, 1 Adapter, 1 Spacer and Case	11.4	5.2	
7904SB	33794	Quick Draw 90 [®] Driver, 2 Draw Studs, 1 Adapter, 1 Spacer and Case	10	4.5	
7906SB	34300	Quick Draw 90 [®] Driver, 1/2" through 2" Slug- Buster [®] Conduit Size Punches and Dies, Draw Studs, 1 Adapter, 1 Spacer and Case	14	6.4	
7904E	34299	Metric – Quick Draw 90 [®] Driver, 2 Draw Studs, 1 Adapter, 1 Spacer and Case	11	5.0	
7904ESB	35615	Metric – Quick Draw 90° Driver, Slug-Buster® Pg Punches and Dies 15.2 mm through 30.5 mm, 2 Draw Studs, 1 Adapter, 1 Spacer and Case	11	5.0	
7904ISO	35616	Metric – Quick Draw 90 [®] Driver, Slug-Buster [®] ISO Punches and Dies 16.2 mm through 40.5 mm, 2 Draw Studs, 1 Adapter, 1 Spacer and Case	12.2	5.5	
34983	34983	Plastic Case			

	STANDARD PUNCHES AND SLUG-BUSTER®							SLUG-SPLITTER SC™			
REQUIRED DRAW STUD AND Accessories	1/2"	3/4"	1-7/32" Oiltight	1"	1-1/4"	1-1/2"	2"	1/2"	3/4"	1-7/32" Oiltight	1-1/4"
3/8" Draw Stud	7////	1									
Spacer & 7/16" Draw Stud											
Spacer & 3/4" Draw Stud		7///	77777	77777	/////]					
3/4" Draw Stud											
10 GA. MILD STEEL			10 GA. STA	INLESS STEI	EL						

R



