T&B[®] Fittings

Industrial Fittings

Electrical Metal Tubing (EMT) Fittings

Pipe Straps – Steel



0.	Size (in.)	Dimensions (in.)			
		Α	В	C (Bolt Hole)	
	1/2	1-27/32	3/4	1/4	
	3/4	2-1/32			
	1	2-11/32			
	1-1/4	2-7/8			
	1-1/2	3-11/16	1-1/4	11/32	
	2	4-1/16	1-1/8	13/32	

4164* Not UL Listed

Cat. No

4159C 4160C 4161C 4162* 4163*

*Not CSA


Conform to CEC 12-1404

Elongated bolt hole makes alignment easy, even when holes in mounting surface are out of alignment. Snap on features hold strap in place.

Pipe Straps – Malleable Iron




Oval Hole for Screw Size (C)



Designed to fit each size of conduit snugly. High reinforcing ribs on each side increase strength, reduce weight. Hot dipped galvanized finish.

Pipe Spacers



Used with T&B conduit straps to permit space between conduit and mounting surface. Eliminates need for costly offset-bending conduit and possible corrosive moisture traps when conduit is mounted directly to a surface. Malleable iron. Hot-dipped galvanized finish, pre-mountable and stackable to eliminate offsetting.

Cat. No.	Size (in.)	Dimensions (in.)		
Gal. NO.		Α	В	C (Bolt Hole)
4176	1/2	2-5/32	2-1/32	1/4
4177	3/4	2-9/16	1-1/16	1/4
4178	1	3	3/4	1/4
4179	1-1/4	3-3/4	1-3/16	5/16
4180	1-1/2	4-3/16	1-5/16	3/8
4181	2	5-3/16	1-1/8	7/16
1282*	2-1/2	5-15/16	1-1/2	1/2
1283*	3	6-11/16	1-5/8	1/2
1284*	3-1/2	7-19/32	1-3/4	5/8
1285*	4	8-5/16	1-7/8	5/8

Not UL Listed

*Not CSA

Conforms to CEC 12-1404



5P

	Size (in.)	Dimensions (in.)		
Cat. No.		Α	В	
1350	1/2, 3/4, 1	3	7/8	
1351	1-1/4,1-1/2, 2	5	1-3/16	
1352	2-1/2, 3	9-9/16	1-3/4	
1353	3-1/2, 4	7-9/16	2	
1354	4-1/2, 5, 6	10-9/16	2-9/16	

Conforms to CEC 12-012 (5)



