

Plug-In RF True Universal Lamp Module

LC2150



Control all dimmable table and floor lamps (up to 300W) with this plug in RF module. Can be linked to and operated by other RFLC devices and controllers, and plugs into any grounded outlet.

features & benefits

- Provides up to a 300W load rating
- Can be used in conjunction with other Legrand RF devices and controllers
- Highly scalable RF lighting control solution

specifications

General Info

Color: White

Size: Unit Package: 2.48"h x 3.03"w x 4.8"d, Master Carton: 9.8"h x 6.7"w x 13.78"d

Housing Material: High Impact Plastic

Special Features: lamp module, remote, Intuity Home Intelligence

Dimensions

Height Metric: 90.98mm

Height U S: 3.582"

Length U S: 1.98"

Length Metric: 50.29mm

Width Metric: 58.72mm

Width U S: 2.312"

Weight: 0.38 lbs

Technical Information

AC Voltage Input: 120V 60Hz
Frequency: Frequency Rating: 900 MHz
Humidity: Up to 90% Relative Humidity (non-condensing)
Load: Max 300W-incandescent, 300W-ELV, 200W-CFL, 200W-LED
Mounting: Plugs into a standard electrical wall outlet
Operating Temperature Celsius: 0° ~ 40°C
Operating Temperature Fahrenheit: 32° ~ 104°F
Regulatory Approvals: UL, FCC, cULus, RoHS