





UL (NEMA) Type 3, 3R, 4, 4X, 12, 13

Lens and Color Selection

| | Color | Incandescent Suffix Code | LED Suffix Code | Catalog Number |
|---|--|-------------------------------------|----------------------------|-----------------------|
| Standard  | Standard—40 mm | | | |
| | Red | C47 | RD | 10250TC47 |
| | Red (EMERG. STOP) | C53 | ED | 10250TC53 |
| | Green | C48 | GD | 10250TC48 |
| | Blue | C49 | LD | 10250TC49 |
| | Amber | C50 | AD | 10250TC50 |
| | White | C51 | WD | 10250TC51 |
| | Clear | C52 | CD | 10250TC52 |
| Side-Lighted Aluminum  | Side-Lighted Aluminum—40 mm ① | | | |
| | Red | C57 | RS | 10250TC57 |
| | Red (EMERG. STOP) | C63 | ES | 10250TC63 |
| | Green | C58 | GS | 10250TC58 |
| | Blue | C59 | LS | 10250TC59 |
| | Amber | C64 | AS | 10250TC64 |
| | Yellow | C60 | YS | 10250TC60 |
| | White | C61 | WS | 10250TC61 |
| | Clear | C62 | CS | 10250TC62 |
| Aluminum Transparent Center  | Aluminum Transparent Center—40 mm ① | | | |
| | Red | C65 | RH | 10250TC65 |
| | Green | C66 | GH | 10250TC66 |
| Jumbo Lens  | Jumbo Lens—50 mm | | | |
| | Red | — | — | 10250TC77 |

Note

① Clear anodized aluminum and colored lens.