

Nylon 6/6 Type CTASST Cable Tie Variety Canisters

UNIRAP™ Cable Tie Variety Canisters

TYPE CTASST

There are times when a variety of lengths and color would be helpful. The Type CTASST Cable Tie Variety Canisters are perfect when your needs change.



G-22

Catalog Number	Contains						Installation Tool	Tool Setting
	Quantity	Color	Max Bundle Diameter	Tensile Strength (lbs)	Length Inches [mm]	Width Inches [mm]		
CTASST	100	Natural	0.75	18	3.94	0.10	CTT50 MK9	2 Std.
	100	UV Black	[19.1]		[100]	[2.5]		
	200	Natural	1.75	50	7.99	0.13	CTT50 MK9	3 Std.
	100	UV Black	[44.5]		[203]	[3.2]		
	50	Natural	3.00	50	11.02	0.19	CTT50 MK9	3 Std.
	50	UV Black	[76.2]		[280]	[4.8]		
CTASST500N	200	Natural	0.75	18	4.00	0.10	CTT50 MK9	2 Std.
	100		[19.1]	30	6.00	0.13		
	200		1.75	50	8.00	0.18	CTT50 MK9	3 Std.
			[44.5]		[203]	[4.5]		
CTASST500B	200	UV Black	0.75	18	4.00	0.10	CTT50 MK9	2 Std.
	100		[19.1]	30	6.00	0.13		
	200		1.75	50	8.00	0.18	CTT50 MK9	3 Std.
			[44.5]		[203]	[4.5]		
CTASST650N	300	Natural	0.75	18	4.00	0.10	CTT50 MK9	2 Std.
	300		[19.1]	50	8.00	0.18		
	50		1.75	50	11.00	0.18	CTT50 MK9	3 Std.
			[44.5]		[203]	[4.5]		
CTASST650B	300	UV Black	0.75	18	4.00	0.10	CTT50 MK9	2 Std.
	300		[19.1]	50	8.00	0.18		
	50		1.75	50	11.00	0.18	CTT50 MK9	3 Std.
			[44.5]		[203]	[4.5]		