

# **MD6 Series**

## Hand-Operated HYTOOL™

Installs full range of connectors #14 - 4/0

- Uses BURNDY® W dies
- Spring loaded positive lock die retainer buttons
- Multiple variations available

#### For Use On:

Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed, and Compact Conductors

#### Taps:

Copper: #10 sol. to 2/0 str.

Aluminum & ACSR: #14 sol. to 4/0 ACSR

#### Stirrups:

#6 to 4/0 ACSR

#### Overhead Full Tension Deadends, Full Tension Splices and Terminals:

#10 str. to 4/0 ACSR

#### **Installs Splices, Taps or Terminations:**

#8 to 500 kcmil Copper Stranded (YA, YA-L, YS, YS-L)

#8 to 350 kcmil Copper Flex

#8 to 350 kcmil Aluminum (YA-A, YS-A)

#### Variations:

Catalog Number: Description:

MD6 Permanent BG (5/8) and D3 grooves; with WO

die (sold separately) can install the CABLELOK

CRIMPIT™ and HYCRIMP™ tap connectors

**MD68** Permanent O and D3 grooves; with WBG die

(sold separately) can install the CABLELOK

CRIMPIT™ and HYCRIMP™ tap connectors

**MD66** Snub-nose, permanent D3 groove only

MD637 Permanent 161, 162, 163, 171 dies in jaw

(J, M&P, T&X)

MD638 Permanent K, BG, C dies in jaw

MD6K Snub-nose, accepts KEARNEY™ type O dies;

using KWADP adapter (sold separately) will

accept BURNDY W and X dies

Hotstick Tools Available - Contact Customer Service



### **Specifications:**

Crimp Force: 4.5 Tons

Life Cycle: Tested over 90,000 cycles with

no adjustments or part replacement

Lenath: 25.50" x 4.50" x 2.00"

Weight: 6.0 lbs Die Style: W and X styles

Warranty: 5 year limited warranty

#### Variations (continued):

Catalog Number: MD64

**Description:** Permanent BG (5/8) and D3 grooves; straight fiberglass handles 24" long; fiberglass rated 100kV

per foot for 5 min.

**MD614** Permanent BG (5/8) and D3 grooves; straight

fiberglass handles 19" long with grips; fiberglass

rated 100kV per foot for 5 min.

**MD612** Permanent O and D3 grooves; straight fiberglass

handles 24" long; fiberglass rated 100kV per foot

for 5 min.

#### Accessories:

Description:

Catalog Number: WBG: Common die set for MD68, MD612 WO: Common die set for MD6, MD64, MD614 KWADP: Adapter to use BURNDY W and X dies with

MD6K variation

WDIETREE: W die holder for 6 die sets

N-56