

**PATCUT245**

**Latch Head, Cu/Al up to 2.45" O.D.**  
Hydraulic Self-Contained Cutter 18V Lithium-Ion

- 180° head rotation
- Cuts up to 2.45" diameter copper/aluminum cable
- Specialized latch style cutting head for interference-free closure for mid-span work
- Ergonomic design, overmolded handle
- Includes 2 batteries, charger, and polymer carrying case
- **EP Enhanced Power** labeled tools accept 2.0, 3.0, 4.0, and 5.0Ah Makita batteries



**For Use On:**

**Copper/Aluminum Cable:**  
Up to 2.45" O.D.

**For Copper and Aluminum cable only. Do not cut steel, ground rod, rebar or guy wire.**

**Variations:** (additional variations may be available)

<b>Catalog Number:</b>	<b>Description:</b>
PATCUT245LI	with 3.0Ah battery
PATCUT245L5	with 5.0Ah battery

**Specifications:**

<b>Output Force:</b>	6 Tons
<b>Tool Weight:</b>	13.7 lbs
<b>Size:</b>	18.13" x 13.50" x 3.50"
<b>Operating Voltage:</b>	18 V-DC Lithium-Ion
<b>Recharge Time:</b>	30 minutes (3.0Ah) 45 minutes (5.0Ah)
<b>Warranty:</b>	5 year limited warranty (excluding blades) Lifetime warranty on INFINITY DRIVE® 3 year on batteries and charger

**Accessories:**

<b>Catalog Number:</b>	<b>Description:</b>
BAT18VLI:	3.0Ah Li-Ion battery
BAT18V5AHLI:	5.0Ah Li-Ion battery
PATCHGRLI:	120V-AC Charger
PATCHGRLIDC:	12/24V-DC Charger
PT208620:	Lanyard
PT10038657:	Replacement Moving Blade
PT10040663:	Replacement Fixed Blade

See Important Notes on Page N-6.