

Non-Metallic Push-In Connectors



NM840



JM84




NMR840

For NM and flexible cord. Easy push-in installation in a new work box*.

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	TRADE SIZE	KO SIZE	UNIT PKG	STD PKG	DIM A	DIM B	DIM C
NM840	54840	3/8	1/2	100	1000	1.031	.375	.965
NM841	54841	1/2	1/2	50	500	1.340	.475	1.125
NM842	54842	3/4	3/4	25	250	1.510	.475	1.200
NM843	54843	1	1	25	250	1.637	.475	1.500
NM844	50175	1-1/4	1-1/4	10	100	2.085	.475	2.012
NMR840*	14940	3/8	1/2	100	1000	1.030	.375	1.060

Refer to pages C-13 and C-14 for complete cable ranges.

*NMR840 can be installed INSIDE or OUTSIDE an installed box, in RETROFIT or NEW WORK.





INSTALLATION INSTRUCTIONS



Disconnect electrical power.
Push the connector into knockout.



Install required cables or cords.



Place wedge in connector slot and lock tight with a pair of pliers. Tightened wedge provides strong, positive grip.

NMR840 RETROFIT INSTALLATION INSTRUCTIONS (Inside Box)



Feed cable through the knockout, then in the connector.



Insert wedge in slot in connector. Lock tight with pliers.



Push assembly into box...



Done!


Non-Metallic Cable Connectors



For non-metallic sheathed cable. One piece construction. Listed for 1 or 2 cables. Holds cables securely and handles a wide range of cable sizes.

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	TRADE SIZE	KO SIZE	UNIT PKG	STD PKG	DIM A	DIM B	DIM C
NM74	54510	3/8	1/2	100	1000	1.289	1.029	.875
NM75	54513	3/4	3/4	25	250	1.289	1.271	1.117

Refer to pages C-13 and C-14 for complete cable ranges. **PATENTED.**





^{*}PATENT PENDING.