



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Decorator Duplex Receptacle

6352A-BU

UPC: 032664628146

Dimensions: 1.32 IN \* .84 IN \* 4.19 IN (L \* W \* H)

Notes: No Data

Warranty: No Data

### Specifications:

- **Type:** Duplex
- **Allowable Wire Size:** #14 to 10 AWG
- **Amperage Rating:** 20A
- **Mounting Type:** Flush
- **Voltage Rating:** 125 Vac
- **Wiring Method:** Back and side
- **Color:** Almond
- **Contact Material:** Brass
- **Design Type:** Receptacle
- **Nema Configuration:** 5-20R
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Receptacle Type:** Two-pole, three-wire, grounding
- **Style Type:** Decorator
- **Connection Type:** Screw
- **Material:** PVC

Supporting documents: No Data

Certifications: No Data

Product compliance: No Data

