### Levels

#### Features:



#### **Magnetic Torpedo Level**



Additional Features:

930-9

901-6

- Magnetized strip on bottom.
- Yellow vials for easy viewing.

Cat. No.	Overall Length	Weight (lbs.)
930-9	9" (229 mm)	.36

# **Folding Rules**



- Strong, 6' (183 cm) long hardwood rules with clear abrasion-resistant coating.
- Black markings on yellow, with red stud center markings every 16 inches.
- Measurements are marked on both sides and both edges, and graduated to 1/16th inch.
- Riveted lock joints are designed for long wear and maintained accuracy.
- Extension slide moves under friction in a T-slot with stops at each end. (Cat. No. 905-6)

Cat. No.	Reading	Length	Weight (lbs.)		
900-6	inside	6' (183 cm)	.33		
901-6	outside	6' (183 cm)	.33		
6-Ft. Folding Rule — with Extension					
905-6	outside	6' (183 cm)	.33		

## **Rare Earth Magnet Torpedo Level**



Additional Features:

931-9RE

- Powerful Rare Earth magnets hold firmly to iron and steel surfaces.
- Rare Earth magnets are up to five times stronger than strip magnets.
- Yellow vials framed with E-Z SEE<sup>®</sup> glow-in-the-dark material for easier viewing in dimly lit areas.

Cat. No.	Overall Length	Weight (lbs.)
931-9RE	9" (229 mm)	.36



- 910-6
- Constructed of tough nylon, reinforced with glass fibers for added durability, and resistance to weather, abrasion, and most chemicals.
- Positive locking joints and stainless steel spring hinges for added strength.
- Measurements are marked on both sides and both edges, graduated to 1/16th inch.
- Black markings on yellow, with red stud center markings every 16 inches.
- Engraved graduations on both sides.

Cat. No.	Reading	Length	Weight (lbs.)
910-6	inside	6' (183 cm)	.33
911-6	outside	6' (183 cm)	.33

All dimensions are in inches and (millimeters) unless otherwise specified.

**AWARNING:** Always wear approved eye protection.