

MY28/MY29 Series

Dieless Mechanical Compression Tools

#8 Str. - 250 kcmil Copper; #8 Str. - 4/0 Str. Aluminum

- Easy to adjust nest die with knurled steel knob and machine threads
- Rugged tool design with heavy duty forged steel with reinforced back and handles
- Bench mount adapter (sold separately) available

For Use On:

Catalog Numbers: MY293, MY293C (covered handles), MY293CF (fully covered)

#8 Str. - 250 kcmil Copper commercial (code) cable
30 Navy - 250 Navy Copper Navy cable
#8 Str. - 4/0 Str. Aluminum commercial (code) cable
Types (Copper): YA, YA-L, YS-L
Types (Aluminum): YA-A, YS-A

Catalog Numbers: MY2911, MY2911C (covered handles), MY29UNIVERSALKIT (MY2911 tool with select connectors)

#8 Str. - 250 kcmil Copper commercial (code) cable
30 Navy - 250 Navy Copper Navy cable
#8 Str. - 4/0 Str. Flexible copper mine machine cable
Types (Copper): YA, YA-L, YS, YAV-FX, YS-L, YAV-L, YSV-L

Catalog Number: MY28

#8 Str. - 4/0 Str. Copper aircraft cable
Types (Copper): YAV-L, YSV-L

Catalog Number: MY284

#8 Str. - 4/0 Str. Aluminum aircraft cable
Types (Aluminum): YAV-A-L, YSV-A-L, YAV-A-R

Catalog Number: MY286

#8 Str. - 2/0 Str. Copper aircraft cable (flexible)
Types (Copper): Nylon Insulated: YAE-L, YAEV-RS, YAEV-H, YAEV-RH



Specifications:

Weight:	8.0 lbs
Size:	22.65" x 4.88" x 1.12"
Die Style:	Dieless
Cycles:	10,000
Warranty:	5 year limited warranty

Accessories:

Catalog Number:	Description:
BMVBCHMT:	Bench Mount Adapter

Close-up of dieless mechanism

