Arlington


Zero to 90[™] Connectors





For use with non-metallic liquid-tight conduit, type B only. Produced from UV rated plastic for long outdoor life.

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	TRADE SIZE	KO SIZE	UNIT PKG	STD PKG	DIM A	DIM B	DIM C	DIM D
NMLT5090	06240	1/2	1/2	10	50	2.765	1.945	2.324	2.387
NMLT7590	06260	3/4	3/4	10	50	3.540	2.590	3.250	2.820
PATENTED. COSTS THE SAME AS OUR "REGULAR" 90° FITTING!			A —				C	E608	2 (£R49636) 12 LR49636



Arlington's no-spin ferrule allows the Zero to 90 connector to be secured to the conduit while fully assembled. To install, simply loosen the tightening nut and screw onto conduit. A positive liquid-tight seal is formed by the pressure sensitive internal gland as the nut is tightened. The sealing ring assures a liquid-tight seal between the fitting and box.

Adjusts for ALL ANGLES... from 0° to 90°!

To adjust the angle simply loosen the center nut, twist to the correct angle, and re-tighten.

