



BURNDY Catalog Number YAV3/0T12B
UPC Number 7818104256333
Description CANLUG-3/0 FLEX-1/2 BELL
Status Active

Web Use
 BURNDY Product Line

Dimensional
 Tongue Angle Straight
 Length (in) 2.22
 Barrell Style Belled
 Bolt Hole Size (in) 0.52
 Barrel Type Standard
 Thickness 0.14
 B Length (in) 0.74
 Pad Width (in) 1.02

General
 Number of Holes 1
 Product Description Pure Electrolytic Seamless Cu Tube Compression Terminal, 1 Hole W/InspWindow, 3/0 AWG Flex, 1/2" Stud, Belled End

Conductor(s)
 Aircraft Cable Size (Range) N/A
 Flex (Class H) Size - Range 3/0 AWG
 Flex (Class I) Size - Range 3/0 AWG
 Copper Solid Size (Range) N/A
 DLO Size (Range) N/A
 Navy Cable Size (Range) N/A
 Copper Stranded (Range) N/A
 Flex (Class G) Size - Range 3/0 AWG
 Flex (Class M) Size - Range 3/0 AWG

Physical
 Type of Plating Tin - Electro Plated
 Bolt Hole Size 1/2
 Plated (Yes or No) Y
 Product Material Copper

Approvals / Certifications
 UL Listed N
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175