FLOOR BOX SYSTEMS

Quick Selection Guide

Wiremold® Floor Boxes are TopGuard protected to meet and exceed the UL scrub water exclusion requirement.



On-Grade Floor Boxes for Concrete Floors

PVC BOXES										
Box Model	Box Type	Service Capability	Box Capacity	Box Construction	Depth Behind Device Plates	K0 Sizes	Cover Model	Cover Construction	Cover & Flange Part Nos.	Notes
Ratchet-Pro 881	Round	Single	1 Gang	PVC	1 3/4" [44mm]	1" Trade Size	Metal, Polycarbonate	Tile, Carpet	895, 896	Flush Devices, On-Grade or Above-Grade
Ratchet-Pro RPNFB	Round	Dual	2 Gangs	PVC	3 1/2" [89mm]	3/4" – 2"	Die-Cast Aluminum	Tile, Carpet	RPAV3CTC, RP7CTC, RPAMD4CTC, RPAMD8CTC, RP4FFCTC, RP9AM2CTC	Surface Devices, On-Grade or Above-Grade
Modulink 880MP2	Rectangular	Single	1 Gang	PVC	1 3/4" [44mm]	1/2" – 2" Trade Size	Metal, Polycarbonate	Tile, Carpet	817, 818, 828, 829, 830 Series	Flush Devices, On-Grade or Above-Grade
Modulink 880MP2	Rectangular	Single	2 or 3 Gangs	PVC	1 3/4" [44mm]	1/2" – 2" Trade Size	Metal, Polycarbonate	Tile, Carpet	827, 828, 829, 830, 837, 838 Series	Flush Devices, On-Grade or Above-Grade

EPOXY PAINTED METAL & CAST IRON BOXES


Box Model	Box Type	Service Capability	Box Capacity	Box Construction	Depth Behind Device Plates	K0 Sizes	Cover Model	Cover Construction	Cover & Flange Part Nos.	Notes
Ratchet-Pro RPSFB-0G	Round	Dual	2 Gangs	PVC	3 1/2" [89mm]	3/4" – 2"	Die-Cast Aluminum	Tile, Carpet	RPAV3CTC, RP7CTC, RPAMD4CTC, RPAMD8CTC, RP4FFCTC, RP9AM2CTC	Surface Devices, On-Grade or Above-Grade
RFB Series RFB2-0G	Rectangular	Triple	2 Gangs	Steel	3" [76mm]	3/4" – 1 1/4" Trade Size	FloorPort™ Die-Cast Aluminum	Tile, Carpet, Wood, Terrazzo	FPCT, FPBT, FPFFT Series	Recessed Devices, Fully Adjustable
RFB Series RFB4-C1-1	Rectangular	Dual	4 Gangs	Cast Iron	2" [51mm]	1" – 1 1/4" Trade Size	FloorPort™ Die-Cast Aluminum	Tile, Carpet	FPCT, FPBT, FPFFT Series	Recessed Devices, Fully Adjustable
RFB Series RFB4E-0G	Rectangular	Triple	4 Gangs	Steel	3 1/2" [89mm]	3/4" – 2" Trade Size	Evolution Round Poke-Thru Cover	Tile, Carpet, Wood, Terrazzo, Bare Concrete	6CT Series	Recessed Devices, Fully Adjustable
RFB Series RFB6-0G	Rectangular	Triple	6 Gangs	Steel	3 1/4" [83mm]	3/4" – 1 1/4" Trade Size	FloorPort™ Die-Cast Aluminum	Tile, Carpet, Wood, Terrazzo	FPCT, FPBT, FPFFT Series	Recessed Devices, Fully Adjustable
RFB Series RFB6E-0G	Rectangular	Triple	6 Gangs	Steel	3 1/4" [83mm]	3/4" – 1 1/4" Trade Size	Evolution™ Round Poke-Thru Cover	Tile, Carpet, Wood, Terrazzo, Bare Concrete	8CT Series	Recessed Devices, Fully Adjustable
RFB Series RFB9-0G	Rectangular	Triple	9 Gangs	Steel	2 1/2" [64mm]	3/4" – 1 1/4" Trade Size	Die-Cast Aluminum	Tile, Carpet, Wood, Terrazzo	RFB119CTC, RFB119BTC	Recessed Devices, Fully Adjustable
RFB Series RFB11-0G	Rectangular	Triple	11 Gangs	Steel	2 1/2" [64mm]	3/4" – 2" Trade Size	Die-Cast Aluminum	Tile, Carpet, Wood, Terrazzo	RFB119CTC, RFB119BTC	Recessed Devices, Fully Adjustable
Evolution Series EFB6S-0G	Rectangular	Triple	6 Gangs	Steel	3 7/8" [98mm]	3/4" – 2" Trade Size	Evolution Rectangular Die-Cast Alumuinum	Tile, Carpet, Wood, Terrazzo, Polished Concrete	EFB610CTC, EFB610BTC, EFB610BT, EFB610CT	Removable Modules, Standard Size Device Plates

FLOOR BOX SYSTEM

FLOORPORT™ SERIES

Wiremold products bearing the TopGuard Protection logo meet or exceed the UL scrub water exclusion requirement.





FloorPort Service Fittings for Resource RFB® Series Floor Boxes, Walkercell® Cellular Raceway, and Walkerdeck Systems provide flexibility in recessed and furniture feed applications.

CODE REFERENCE

cULus Listed Metallic Outlet Boxes: File E2961, Guide QCIT

cULus Listed Outlet Boxes & Fittings Classified for Fire Resistance: File R8209, Guide CEYY

Meets Article 341.40, 314.41 & 374 of NEC



New FloorPort[™] Series Cover Assemblies feature a full 180° opening coverwith a new recessed handle for easier opening and new cable egress openings that protect cabling while holding them securely in place.



COLOR OPTIONS













FloorPort Series Service Fittings are available in aluminum, black, brass, bronze, gray and nickel as indicated in the part number description.

SERVICE FITTINGS & ACTIVATION ACCESSORIES

FLOORPORT™ SERIES

FloorPort™ Series Flanged Cover Plates Ordering Informmation

Floorport Part Number Configurator


<u>F P</u>			
FloorPort Series:	Cover Style: Blank Top = B Cutout Top = C Furniture Feed = FF	Top Style: Tile (flangeless) = T Tile/Carpet = TC (flanged)	Cover Color: Brushed Aluminum = AL Black = BK Brass = BS Bronze = BZ Gray = GY Nickel = NK

Load Capacities for FloorPort Cover Assemblies

CATALOG NUMBERS	MAXIMUM LOAD IN POUNDS
FPCTC	1000
FPBTC	750
FPFFT	1000

NOTE: Load applied through a 2" [51mm] mandrel in center of service fitting. Loads above are static loads only and do not pertain to rolling loads.


FPCTC Cutout Cover Assembly



FPCTCBK, FPCTCBZ, FPCTCBS, FPCTCNK, FPCTCGY, FPCTCAL

Flanged cover for use in tile or carpet installation. Die-cast aluminum assembly available in black, bronze, brass, nickel, gray or brushed aluminum. Insert in lid allows for carpet or tile cutouts to match finished floor.


FPFFTC Furniture Feed Cover Assembly



FPFFTCBK, FPFFTCBZ, FPFFTCBS, FPFFTCNK, FPFFTCGY, FPFFTCAL

Flanged cover for use in tile or carpet installation. Die-cast aluminum assembly available in black, bronze, brass, nickel, gray or brushed aluminum. Provided with one 1" trade size screw plug for power or communication type cabling and one combination 1 1/4" and 2" trade size screw plug for communication type cabling. Allows for feeding both power and communication cabling.

FPBTC Blank Cover Assembly




FPBTCBK, FPBTCBZ, FPBTCBS, FPBTCNK, FPBTCGY, FPBTCAL

Flanged cover for use in tile or carpet installation. Die-cast aluminum assembly available in black, bronze, brass, nickel, gray, or brushed aluminum. Lid area is flush with the finished floor, no cutouts provided.

FloorPort™ Series Flangeless Cover Assemblies Ordering Information


FPCT Cutout Cover Assembly



FPCTCBK, FPCTCBZ, FPCTCBS, FPCTCNK, FPCTCGY, FPCTCAL

Flangeless cover for use in tile or carpet installations. Die-cast aluminum assembly available in black, bronze, brass, nickel, gray, or brushed aluminum. Insert in lid allows for carpet or tile cutouts to match finished floor.


FPFT Furniture Feed Cover Assembly



FPFFTCBK, FPFFTCBZ, FPFFTCBS, FPFFTCNK. FPFFTCGY. FPFFTCAL

Flangeless cover for use in tile or carpet installation. Die-cast aluminum assembly available in black, bronze, brass, nickel, gray, or brushed aluminum. Provided with one 1" trade size screw plug for power or communication type cabling and one combination 1 1/4" and 2" trade size screw plug for communication type cabling. Allows for feeding both power and communication cabling.

FPBT Blank Cover Assembly



FPBTCBK, FPBTCBZ, FPBTCBS, FPBTCNK, FPBTCGY, FPBTCAL

Flangeless cover for use in tile or carpet installation. Die-cast aluminum assembly available in black, bronze, brass, nickel, gray, or brushed aluminum. Lid area is flush with the finished floor, no cutouts provided.