












SIRIUS 3SE5 Mechanical Position Switches

3SE5, plastic enclosures
Enclosure width 31 mm according to EN 50047

| Version | Diameter | DT | Modular system | PU (UNIT, SET, M) | PS* | PG | |
|---|---|--|----------------------|----------------------|----------------------|--------|--------|
| | mm | | Article No. | Price per PU | | | |
| Operating mechanisms | | | | | | | |
|  | Roller plungers, type C acc. to EN 50047 | | | | | | |
| | Plastic rollers | 10 | ⊕ A | 3SE5000-0AD03 | 1 | 1 unit | 41K |
| | High-grade steel rollers | 10 | ⊕ B | 3SE5000-0AD04 | 1 | 1 unit | 41K |
|  | Roller plungers with central fixing | | | | | | |
| | Plastic rollers | 10 | ⊕ B | 3SE5000-0AD10 | 1 | 1 unit | 41K |
| | High-grade steel rollers | 10 | ⊕ B | 3SE5000-0AD11 | 1 | 1 unit | 41K |
|  | Roller levers, type E acc. to EN 50047 | | | | | | |
| | Metal lever, plastic roller | 13 | ⊕ A | 3SE5000-0AE10 | 1 | 1 unit | 41K |
| | Metal lever, high-grade steel roller | 13 | ⊕ B | 3SE5000-0AE11 | 1 | 1 unit | 41K |
| | High-grade steel lever, plastic roller | 13 | ⊕ B | 3SE5000-0AE12 | 1 | 1 unit | 41K |
| | High-grade steel lever, high-grade steel roller | 13 | ⊕ B | 3SE5000-0AE13 | 1 | 1 unit | 41K |
|  | Angular roller levers | | | | | | |
| | Metal lever, plastic roller | 13 | ⊕ A | 3SE5000-0AF10 | 1 | 1 unit | 41K |
| | Metal lever, high-grade steel roller | 13 | ⊕ B | 3SE5000-0AF11 | 1 | 1 unit | 41K |
| | High-grade steel lever, plastic roller | 13 | ⊕ A | 3SE5000-0AF12 | 1 | 1 unit | 41K |
| | High-grade steel lever, high-grade steel roller | 13 | ⊕ B | 3SE5000-0AF13 | 1 | 1 unit | 41K |
|  | Spring rods (for switches with snap-action contacts only) | | | | | | |
| | Plunger made of plastic, spring of high-grade steel: 7 | | | | | | |
| | | • Length 142.5 mm (spring 50 mm, plunger 50 mm) | B | 3SE5000-0AR01 | 1 | 1 unit | 41K |
| | | • Length 76 mm (spring 23.5 mm, plunger 10 mm) | B | 3SE5000-0AR03 | 1 | 1 unit | 41K |
| | | • Length 242.5 mm (spring 150 mm, plunger 50 mm) | B | 3SE5000-0AR04 | 1 | 1 unit | 41K |
| | Plunger and spring made of high-grade steel: 7 | | | | | | |
| | • Length 142.5 mm (spring 50 mm, plunger 50 mm) | B | 3SE5000-0AR02 | 1 | 1 unit | 41K | |
| Twist actuators | | | | | | | |
|  | Twist actuators, plastic (without lever) | | | | | | |
| | Switching right and/or left, adjustable | | ⊕ A | 3SE5000-0AK00 | 1 | 1 unit | 41K |
|  | Levers | | | | | | |
| | Twist levers 21 mm, straight, type A according to EN 50047 | | | | | | |
| | Metal lever, plastic roller | 19 | ⊕ A | 3SE5000-0AA21 | 1 | 1 unit | 41K |
| | Metal lever, high-grade steel roller | 19 | ⊕ B | 3SE5000-0AA22 | 1 | 1 unit | 41K |
| | Metal lever, high-grade steel roller with ball bearing | 19 | ⊕ B | 3SE5000-0AA23 | 1 | 1 unit | 41K |
| | Metal lever, plastic roller | 30 | ⊕ B | 3SE5000-0AA25 | 1 | 1 unit | 41K |
| | High-grade steel lever, plastic roller | 19 | ⊕ B | 3SE5000-0AA31 | 1 | 1 unit | 41K |
| | High-grade steel lever, high-grade steel roller | 19 | ⊕ B | 3SE5000-0AA32 | 1 | 1 unit | 41K |
|  | Twist levers 30 mm, straight¹⁾ | | | | | | |
| | Metal lever, plastic roller | 19 | ⊕ B | 3SE5000-0AA24 | 1 | 1 unit | 41K |
| | Metal lever, plastic roller | 30 | ⊕ B | 3SE5000-0AA26 | 1 | 1 unit | 41K |
|  | Twist levers, adjustable length, with grid hole | | | | | | |
| | Metal lever, plastic roller | 19 | ⊕ B | 3SE5000-0AA60 | 1 | 1 unit | 41K |
| | Metal lever, high-grade steel roller | 19 | ⊕ B | 3SE5000-0AA61 | 1 | 1 unit | 41K |
| | Metal lever, plastic roller | 50 | ⊕ B | 3SE5000-0AA67 | 1 | 1 unit | 41K |
| | Metal lever, rubber roller | 50 | ⊕ B | 3SE5000-0AA68 | 1 | 1 unit | 41K |
| | High-grade steel lever, plastic roller | 19 | ⊕ B | 3SE5000-0AA62 | 1 | 1 unit | 41K |
| | | High-grade steel lever, high-grade steel roller | 19 | ⊕ B | 3SE5000-0AA63 | 1 | 1 unit |
|  | Twist levers, adjustable length | | | | | | |
| | Metal lever, plastic roller | 19 | A | 3SE5000-0AA50 | 1 | 1 unit | 41K |
| | Metal lever, high-grade steel roller | 19 | B | 3SE5000-0AA51 | 1 | 1 unit | 41K |
| | Metal lever, plastic roller | 30 | B | 3SE5000-0AA55 | 1 | 1 unit | 41K |
| | Metal lever, plastic roller | 50 | B | 3SE5000-0AA57 | 1 | 1 unit | 41K |
| | Metal lever, rubber roller | 50 | B | 3SE5000-0AA58 | 1 | 1 unit | 41K |
| | High-grade steel lever, plastic roller | 19 | B | 3SE5000-0AA52 | 1 | 1 unit | 41K |
| | | High-grade steel lever, high-grade steel roller | 19 | B | 3SE5000-0AA53 | 1 | 1 unit |
|  | Rod actuators | | | | | | |
| | Aluminum rod, length 200 mm | 6 | B | 3SE5000-0AA80 | 1 | 1 unit | 41K |
| | Spring rod, length 200 mm | 6 | B | 3SE5000-0AA81 | 1 | 1 unit | 41K |
| | Plastic rod, length 200 mm | 6 | B | 3SE5000-0AA82 | 1 | 1 unit | 41K |

⊕ Positively driven actuator, necessary in safety circuits.

¹⁾ Can be clinch mounted (turned through 180°, rear of lever).