

## Automatic Electrical Tester



- Hassle-free, automatic measurement of amperage, voltage and resistance.
- Low impedance eliminates stray or "ghost" voltage readings.
- True RMS for the most accurate measurement when harmonics are present.
- High resolution, auto-illuminating LCD backlit display.
- Auto off for longer battery life.
- Resistance measurement.
- Audible continuity test.
- Diode test
- Data hold to capture measurements.
- Accessories included: (1) 9 V battery, test leads and carrying case.
- Lifetime Limited Warranty.

### SPECIFICATIONS

<b>Amperage Measurement</b>	ACA 0.9 to 600.0
<b>Voltage Measurement</b>	AC V: 1.3 to 999.9; DC V: 2.1 to 999.9; -0.7 to -999.9
<b>Resistance</b>	999Ω; 9.999kΩ
<b>Display</b>	10,000-count LCD
<b>Jaw Opening</b>	1.34" (34 mm)
<b>Measurement Category</b>	CAT IV, 600 V; CAT III, 1000 V

CAT. NO.	UPC NO.	DESCRIPTION
CMT-90	12123	Electrical Tester, 1000V, 600A
00606	00606	Test Leads
TC-10	07534	Carrying case



## Automatic Electrical Tester



- Hassle-free, automatic measurement of amperage, voltage, and resistance.
- Low impedance eliminates stray or "ghost" voltage readings.
- Compact design for measuring in tight spaces.
- Resistance measurement
- Audible continuity test
- Diode test
- Data hold to capture important readings.
- Auto off for longer battery life.
- Accessories included: (1) 9 V battery, test leads, carrying case.
- Lifetime Limited Warranty.

### SPECIFICATIONS

<b>Amperage Measurement</b>	0.9 - 400.0A AC
<b>Voltage Measurement</b>	AC V: 1.3-600.0V; DC V: 2.1-600.0; -0.7 to -600.0V
<b>Resistance</b>	999Ω; 9.999kΩ
<b>Display</b>	10,000-count LCD
<b>Jaw Opening</b>	1.06" (27 mm)
<b>Measurement Category</b>	CAT III, 600V

CAT. NO.	UPC NO.	DESCRIPTION
CMT-80	07735	Electrical Tester
11372	11372	Test Leads
TC-5	07588	Carrying case

