

# AUDIO | VIDEO CONNECTIVITY

## TracJack® Solutions

### TracJack Solutions

TracJack footprint is front loading and supports a number of A/V and data modules. It's ideal for combining A/V with our high performance Clarity® workstation products.



PART NO.	DESCRIPTION
OR-63700058	RCA red, female to female
OR-63700086	RCA green, female to female
OR-63700085	RCA blue, female to female
OR-63700059	RCA white, female to female
OR-63700060	RCA yellow, female to female
OR-63700071	RCA red to 110
OR-63700083	RCA green to 110
OR-63700084	RCA blue to 110
OR-63700070	RCA white to 110
OR-63700047	RCA yellow to 110
OR-63700046	Pair of RCA to 110 (one red, one black), 180° exit
OR-63700025	S-Video to 110
OR-63700069	3.5mm stereo jack
OR-63700023	BNC 75 ohm, female to female
OR-63700006	F Conn 75 ohm, female to female
OR-63700087	F Conn 75 ohm, recessed, female to female
OR-63700021	Speaker term set, red, black pair
OR-42100002	Package of ten blanks

NOTE: Standard color for plastic TracJack faceplates is fog white. For electrical ivory add -13, for white add -88 and for Wiremold® ivory add -99 to end of part number. For other colors, contact sales.

# WORKSTATION SYSTEMS

## TracJack® Modules & Faceplates



### TracJack Modules

TracJack is a versatile single-module solution—the perfect combination of high quality, enhanced performance, labor savings, ease of use, and flexibility in design. TracJack front removable snap-in modules make moves, adds, and changes easy. TracJack products are compatible with Fib-or-Cop II and the complete line of TracJack faceplates and surface mount boxes. TracJack modules are available in LC, SC, ST, FC, and MT-RJ styles in order to suit any installation requirement.

Features	Benefits
■ Snap-in module	■ Simple, secure installation
■ Modular design	■ Flexibility in structured cabling system design
■ Front removable	■ Facilitates quick moves, adds, and changes
■ No special tools required	■ Reduced installation expense
■ Fully compatible with all TracJack faceplates	■ Provides wide range of design possibilities

### TracJack Modules

PART NO.	DESCRIPTION
OR-63700039*	1-LC (2 fibers) multimode, beige adapter, phosphor-bronze alignment sleeves, 180° exit, flush, 1 unit
OR-63700050	1-LC (2 fibers) multimode, beige adapter, phosphor-bronze alignment sleeves, 45° angled exit, 2 units
OR-63700075*	1-LC (2 fibers) multimode, aqua adapter, ceramic alignment sleeves, 180° exit, flush, 1 unit
OR-63700017*	1-SC simplex multimode, beige adapter, phosphor-bronze alignment sleeves, 180° exit, flush, 1 unit
OR-63700066*	2-SC simplex multimode, beige adapters, phosphor-bronze alignment sleeves, 180° exit, 1 unit
OR-63700051	1-SC simplex multimode, beige adapter, phosphor-bronze alignment sleeves, 45° angled exit, flush, 2 units
OR-63700078*	1-SC simplex multimode, aqua adapter, ceramic alignment sleeve, 180° exit, flush, 1 unit
OR-63700011	1-ST simplex multimode, metal adapter, phosphor-bronze alignment sleeves, 180° exit, 1 unit
OR-63700013	2-ST multimode, metal adapter, phosphor-bronze alignment sleeves, 180° exit, 1 unit
OR-63700026	1-MT-RJ (2 fibers) feed-through, multimode, beige adapter, 180° exit, flush, 1 unit
OR-63700048	1-MT-RJ (2 fibers) feed-through, multimode, beige adapter, 45° angled exit, 2 units
OR-63700080	1-LC (2 fibers) multimode, aqua adapter, ceramic alignment sleeves, 45° angled exit, 2 units
OR-63700081	2-SC simplex multimode, aqua adapters, ceramic alignment sleeves, 180° exit, 1 unit
OR-63700082	1-SC simplex multimode, aqua adapter, ceramic alignment sleeves, 45° angled exit, 2 units

NOTE: Consult sales at 800-934-5432 for single-mode part numbers.

	-00	-25	-42	-43	-44	-45	-68	-78	-88	-99
fog white	WM						WM	WM	WM	ivory WM

\*Also available in black, red, orange, yellow, green, light green, WM light gray, WM gray, white and WM ivory. housing colors: -00, -25, -42, -43, -44, -45, -68, -78, -88, -99