Portable Printers

BradyID.com/s34

Portable Printer Comparison Guide

Use the following comparison guide to quickly see which printer best fits your application needs. Then turn to the following pages to find out more about each printer, compatible materials and print ribbons.





BMP®41 Label Printer

BradyID.com/bmp41





Online Video!

Visit BradylD.com/bmp41 for more information or to view an online printer demo video.

Your Complete Printing Solution:

BMP41 cartridges with label and print ribbon.....page 298

BMP®41 Label Printer & Accessories

Catalog #	Description
BMP41	BMP41 Label Printer with Hard Case*
BMP41-KIT-VD	BMP41 Printer DataComm Starter Kit*
BMP41-KIT-EL	BMP41 Printer Electrical Starter Kit*
BMP41-KIT-GI	BMP41 Printer Facility ID Starter Kit*
BMP41-BATT	BMP41 Rechargeable Battery Pack
BMP41-QC	BMP41 External Battery Quick Charger
BMP41-AC	BMP41 AC Adapter / Battery Charger
BMP41-MAGNET	BMP41 Magnet Accessory
BMP41-HC	BMP41 Hard Case
BMP41-USB	BMP41 USB Cable

*Printer ships with BMP41 printer, NiMH battery, AC adapter / charger, hard case, MC1-1000-595-WT-BK cartridge, USB cable, product & drivers CD, and quick start quide

BMP®41 LABEL PRINTER

ONE AND DONE. BMP®41 Printer Does It All!

A rugged, handheld labeling solution that gives you the versatility of die-cut labels and continuous labels in one printer!


- Quick-load, drop-in cartridges for quick supply change and automatic label formatting
- Fast print speed of 1.3" per second
- Over 100 label parts in 11 materials
- 3/4" sleeves and 1" wide continuous output
- Drop tested rugged industrial bumpers with a grab and go grip to be on the move with you
- Large graphical LCD display with backlight to see exactly what you're printing
- Rechargeable NiMH battery, AA or AC adapter, for long lasting power supply
- Built-in wizard-style apps for wire ID, cabel flags, terminal blocks, patch panels, breaker boxes and general ID





BMP®41 Printer S	nacifications
	pecilications
Max Labels Per Day	Average 250 labels/day
Print Resolution	300 dpi
Print Technology	Thermal transfer
Print Speed	133mm/sec (1.3in/sec)
Tape Widths	Various sizes from
(inches)	0.235" to 1.0"
Tape Widths	Various sizes from
(mm)	5.969 mm to 25.4 mm
Max Label Width	1.00" (25.4mm)
Max Print Width	0.96" (24.4 mm)
	48 MB / Up to 25,000
Memory	Labels
Materials Supported	M-, MC-, MC1- Series Cartridges (1.00" and 0.75" height only) 100+ Stock Parts
Continuous vs Die Cut Labels	Continuous and die cut labels
Connectivity Options	Yes
PC Connectivity	USB
Software Compatibility	Optional through USB
File Transfer from	Yes - with Labelmark®
PC to printer	Software
Wireless	No
Connectivity	
Stand Alone Printing	Yes
Color Capability	Single print color on a label
Keyboard	QWERTY
Backlit Screen	2.5" x 1.4", user adjustable
	backlit
Text Sizes	4 to 103pt + autosizing
Multi-Line Print	Yes
Print Rotation	Yes
Serialization	Yes
Barcode	39 and 128
Symbols Categories	450
Portability	Yes
Label Types or Application Functions	Adhesive Polyester, PermaSleeve® Heat Shrink Tubing, Polypropylene Tags, Self-laminating Vinyl, Metallized Polyester Ultra Aggressive Polyester, Repositional Vinnl Cloth, Nylon Cloth, Reflective Tape, Indoor/Outdoor Vinyl,
Applications	Basic and Die Cut labels for Wire and Cable ID, Datacomm and AV labeling, Electrical ID, Panel ID, Product ID, Facility ID, Safety and Maintenance, General ID

Exceptional material variety and durability.





Labelina



Labels



Communications





Power Supply

Weight

Warranty



AC Power, rechargable

NiMH battery

2 years

2.6 lbs (1.2 kg)

PermaSleeve® Wire Marking

Indoor / Outdoor Vinyl Labels...and more!

